


LM WO 25.4/57 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	LaserMark, Conductor and cable markers, 5.9 - 12.3 mm, 25.4 x 57 mm, white
Order No.	1768380000
Type	LM WO 25.4/57 WS
GTIN (EAN)	4032248110025
Qty.	10 pc(s).

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	57 mm	Width (inches)	2.244 inch
Net weight	10 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate	Colour	white
Halogen	No	Material	Polyester film
Material colour according to resistance code	9	Number of markers per combination	1 Label sheet = 35 Conductor and cable markers
Number per sheet	35	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	25.4 x 18 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	57 mm		

Conductor and cable markers

Conductor O.D.	5.9 - 12.3 mm	Conductor O.D., max.	12.3 mm
Conductor O.D., min.	5.9 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	25 mm ²	Cross-section for connected wire	25 - 120 mm ²
Halogen	No	Text field height	18.5 mm
Text field width	25.4 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Catalogues	Catalogues in PDF-format

LM WO 25.4/57 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1768380000](#)