

**AP MCZ1.5 1674****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

**General ordering data**

|            |                                                                                    |
|------------|------------------------------------------------------------------------------------|
| Version    | Small housing, OMNIMATE Housing - TERMINALBOX grey-beige, End plate, Width: 1.5 mm |
| Order No.  | <a href="#">8389030000</a>                                                         |
| Type       | AP MCZ1.5 1674                                                                     |
| GTIN (EAN) | 4008190386849                                                                      |
| Qty.       | 50 pc(s).                                                                          |

## AP MCZ1.5 1674

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Height     | 55.85 mm | Height (inches) | 2.199 inch |
| Width      | 1.5 mm   | Width (inches)  | 0.059 inch |
| Length     | 91 mm    | Length (inches) | 3.583 inch |
| Net weight | 5.961 g  |                 |            |

## General data

|                   |            |                      |     |
|-------------------|------------|----------------------|-----|
| Colour            | grey-beige | Encapsulation option | Yes |
| Protection degree | IP20       |                      |     |

## Material data

|                                  |           |                           |            |
|----------------------------------|-----------|---------------------------|------------|
| Comparative Tracking Index (CTI) | 600 ≤ CTI | Insulating material       | Wemid (PA) |
| Insulating material group        | IIIa      | UL 94 flammability rating | V-0        |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ECLASS 9.1  | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |

## Approvals

Approvals



ROHS

Conform

## Downloads

|                  |                                                                                                                                                                                                                                                                                                                   |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                   |
| Engineering Data | <a href="#">WSCAD, Zuken E3.S</a>                                                                                                                                                                                                                                                                                 |
| Catalogues       | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                          |
| Brochures        | <a href="#">FL ANALO.SIGN.CONV. EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a> |


### AP MCZ1.5 1674

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Drawing



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[8389030000](#)