

KT 12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

Version	Cutting tools, Cutting tool for one-hand operation
Order No.	9002660000
Type	KT 12
GTIN (EAN)	4008190181970
Qty.	1 pc(s).

KT 12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	63.5 mm	Height (inches)	2.5 inch
Width	225 mm	Width (inches)	8.858 inch
Weight	300 g	Net weight	331.7 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Cutting tool for up to 12 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Copper cable - flexible, max.	35 mm ²	Copper cable - flexible, max. (AWG)	2 AWG
Copper cable - solid, max.	16 mm ²	Copper cable - solid, max. (AWG)	6 AWG
Copper cable - stranded, max.	25 mm ²	Copper cable - stranded, max. (AWG)	3 AWG
Copper cable, max. diameter	12 mm	Data / telephone / control cable, max. Ø	12 mm
Single-core aluminium cable, max.(mm ²)	25 mm ²	Stranded aluminium cable, max (mm ²)	25 mm ²
Stranded aluminium cable, max. (AWG)	6 AWG	Stranded aluminium cable, max. diameter	8 mm

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ECLASS 9.0	21-04-47-01
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-47-01
ECLASS 11.0	21-04-47-01		

Approvals

Approvals



Downloads

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Cable cutters
Catalogues	Catalogues in PDF-format
Brochures	

KT 12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9002660000](#)