

KT 45 R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Version	Cutting tools, Circular cable cutter
Order No.	9202040000
Type	KT 45 R
GTIN (EAN)	4032248482160
Qty.	1 pc(s).

KT 45 R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	85 mm	Height (inches)	3.346 inch
Width	290 mm	Width (inches)	11.417 inch
Weight	740 g	Net weight	980 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	Front cable cutter up to 45 mm outer diameter	Version	One-hand mechanical
------------------------	---	---------	---------------------

Cutting tools

Aluminium sector cable	4 x 70 SE	Copper cable - flexible, max.	400 mm ²
Copper cable - flexible, max. (kcmil)	800 kcmil	Copper cable - stranded, max.	300 mm ²
Copper cable - stranded, max. (kcmil)	600 kcmil	Copper cable, max. diameter	45 mm
Copper sector cable	3 x 70 SM	Data / telephone / control cable, max. Ø	45 mm
Stranded aluminium cable, max (mm ²)	400 mm ²	Stranded aluminium cable, max. (kcmil)	800 kcmil
Stranded aluminium cable, max. diameter	45 mm		

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ECLASS 9.0	21-04-47-01
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-47-01
ECLASS 11.0	21-04-47-01		

Approvals

Approvals



Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

KT 45 R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use

-  Cu + Al: max. 45 mm
-  Cu: max. 300 mm²
Al: max. 400 mm²
-  Cu: max. 400 mm²



KT 45 R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****KT 45 R**

Cutting tools in mechanical ratchet version. Suitable for non-pinch cutting of copper and aluminium conductors. Easy operation thanks to optimum leverage and a cleverly engineered cam mechanism.

General ordering data

Type	ERME KT 45 R	Version
Order No.	9204270000	Replacement parts
GTIN (EAN)	4032248640973	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9202040000](#)