

# BGA Heat Sink (High Aspect Ratio Ext.) Straight Fin



ATS Part#: **ATS010010007-SF-1F**  
 Description: 10.00 x 10.00 x 7.00 mm BGA Heat Sink (High Aspect Ratio Ext.) Straight Fin  
 Heat Sink Type: **Straight Fin**  
 Heat Sink Attachment: **N/A**  
 Equivalent Part Number: **N/A**

*\*Image above is for illustration purpose only.*

## Features & Benefits

- High aspect ratio, straight fin heat sinks that are ideal for compact PCB environments
- Fabricated from extruded aluminum, which minimizes thermal resistance from the base to the fins, reduces weight and keeps costs low
- Higher performance helps ensure reliable product life at a lower cost than other extruded heat sinks
- Comes standard without interface material or with most common pressure sensitive thermal tapes as a custom option

## Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	44.41 °C/W	37.7 °C/W	33.4 °C/W	30.4 °C/W	28 °C/W	26.2 °C/W	24.6 °C/W
	Ducted Flow	30.9	26	22.9	20.8	19.2	17.9	16.9

## Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	10.00 mm	10.00 mm	7.00 mm	10 mm	N/A	BLACK-ANODIZED
<b>Notes:</b> <ul style="list-style-type: none"> <li>• Dimension <b>A</b> and <b>B</b> refer to component size.</li> <li>• Dimension <b>C</b> is the heat sink height from the bottom of the base to the top of the fin field.</li> <li>• Dimension <b>D</b> is fin tip to fin tip.</li> <li>• Thermal performance data are provided for reference only. Actual performance may vary by application.</li> <li>• ATS reserves the right to update or change its products without notice to improve the design or performance.</li> <li>• ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.</li> <li>• Contact ATS to learn about custom options available.</li> </ul>						

*\*Image above is for illustration purpose only.*

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), [sales@qats.com](mailto:sales@qats.com) or [www.qats.com](http://www.qats.com).

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Rev - 100214

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Thermal Solutions:](#)

[ATS010010007-SF-1F](#)