


# BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD



*\*Image above is for illustration purpose only.*

ATS Part#:	ATS-50450B-C1-R0
Description:	45.00 x 45.00 x 7.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD
Heat Sink Type:	maxiFLOW
Heat Sink Attachment:	maxiGRIP
Equivalent Part Number:	ATS-50450B-C2-R0


## Features & Benefits

- maxiFLOW™ design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- maxiGRIP™ attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- Comes preassembled with high performance thermal interface material
- Designed for standard height components from 3 to 4.5mm

## Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	4 °C/W	2.9 °C/W	2.4 °C/W	2.1 °C/W	1.9 °C/W	1.8 °C/W	1.6 °C/W
	Ducted Flow	2.6	N/A	N/A	N/A	N/A	N/A	N/A

## Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
	45.00 mm	45.00 mm	7.50 mm	61.5 mm	T412	BLUE-ANODIZED
<p><b>Notes:</b></p> <ul style="list-style-type: none"><li>Dimension <b>A</b> and <b>B</b> refer to component size.</li><li>Dimension <b>C</b> is the heat sink height from the bottom of the base to the top of the fin field.</li><li>ATS-50450B-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint-Gobain C675).</li><li>Thermal performance data are provided for reference only. Actual performance may vary by application.</li><li>ATS reserves the right to update or change its products without notice to improve the design or performance.</li><li>ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.</li><li>Optional maxiGRIP™ Installation/Removal Tool Set P/N: <b>MGT450</b></li><li>Contact ATS to learn about custom options available.</li></ul>						

*\*Image above is for illustration purpose only.*

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), [sales@qats.com](mailto:sales@qats.com) or [www.qats.com](http://www.qats.com).

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



**ATS** ADVANCED  
THERMAL  
SOLUTIONS, INC.  
Innovations in Thermal Management®

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Thermal Solutions:](#)

[ATS-50450B-C1-R0](#)