

PLUG COVER: ND-2P2-009-JC
RECEPTACLE COVER: ND-2R2-009-TH
 XX-XXX-XXX-XX

PLUG COVER		RECEPTACLE COVER	
SERIES			
ND .025" Metal Dust Cover		ND .025" Metal Dust Cover	
BODY			
2 2-Row		2 2-Row	
BODY STYLE: P Plug cover		BODY STYLE: R Receptacle cover	
BODY PLATING: 2 Electroless nickel 3 Electrodeposited cadmium <input checked="" type="checkbox"/>		BODY PLATING: 2 Electroless nickel 3 Electrodeposited cadmium <input checked="" type="checkbox"/>	
SIZE			
XXX 009, 015, 021, 025, 031, 037, 051, 065, 069 or 085		XXX 009, 015, 021, 025, 031, 037, 051, 065, 069 or 085	
HARDWARE			
STYLE OF HARDWARE: JC Turning jackscrews, captivated #0-80 UNF* TH Threaded hole, #0-80 UNF*		STYLE OF HARDWARE: JC Turning jackscrews, captivated #0-80 UNF* TH Threaded hole, #0-80 UNF*	

* = #2-56 UNC thread on 85 position covers
 .050 hex key (#0-80 thread)
 1/16" hex key (#2-56 thread)
 Recommended torque value 1.0 inch-lbs. max. (#0-80 thread)
 Recommended torque value 2.0 inch-lbs. max. (#2-56 thread)
 Ball end hex wrench not recommended
 Hex wrench key/bit conforming to the requirements of ASME / ANSI-B-18.3 is recommended.
 .050" hex L-key long arm wrench - order AirBorn p/n CDG14148.
 1/16" hex L-key long arm wrench - order AirBorn p/n CDG14160.

☒ = Option not RoHS compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

AirBorn:

[ND-2P2-031-JC](#) [ND-2P2-065-JC](#) [ND-2R2-009-JC](#) [ND-2R2-021-JC](#) [ND-2R2-037-JC](#) [ND-2R2-051-TH](#) [ND-2R2-025-JC](#) [ND-2R2-069-JC](#) [ND-2R2-069-TH](#) [ND-2R2-085-JC](#) [ND-2R2-085-TH](#) [ND-2R2-015-TH](#) [ND-2R2-021-TH](#) [ND-2R2-009-TH](#) [ND-2R2-015-JC](#) [ND-2R2-031-TH](#) [ND-2R2-037-TH](#) [ND-2R2-051-JC](#) [ND-2R2-065-TH](#) [ND-2P2-051-TH](#) [ND-2P2-065-TH](#) [ND-2P2-069-JC](#) [ND-2P2-069-TH](#) [ND-2P2-085-TH](#) [ND-2P3-025-TH](#) [ND-2P2-015-JC](#) [ND-2P2-015-TH](#) [ND-2P2-021-JC](#) [ND-2P2-021-TH](#) [ND-2P2-025-TH](#) [ND-2P2-051-JC](#) [ND-2R2-065-JC](#) [ND-2P2-025-JC](#) [ND-2P2-037-JC](#) [ND-2P2-037-TH](#) [ND-2P2-009-JC](#) [ND-2P2-009-TH](#)