


# AX60501

## 6-slot ShoeBox Chassis

### Features

- Desktop or wallmount industrial computer chassis
- One 5.25" and two 3.5" HDD drive bays
- Equipped with a PS/2 type power supply



Equipped with a power supply bracket securing the power supply better when the chassis is positioned in 90° orientation

▲ Top view

### Specifications

Standard Color	Beige
Construction	Heavy-duty steel
Drive Capacity	Exposed 1 x 5.25" HDD drive bay 1 x 3.5" HDD drive bay Internal 1 x 3.5" HDD drive bay
Cooling	1 x 9 cm ball-bearing fan (51 CFM/each) with a removable filter
Front Panel Indicators	1 x Power on/off
Front Panel Controls	1 x Power on/off 1 x System reset
Front Panel Connector	1 x PS/2 6-pin keyboard & mouse 2 x USB
System Board	SBCs
Expansion Interface	6-slot backplane
Operating Temperature	0°C to +40°C (+32°F to +104°F)
Dimensions	235 ± 1.0mm (9.25") (W) x 400.5 ± 1.0mm (15.77") (D) x 154.7 ± 1.0mm (6.09") (H)
Weight (net/gross)	9 kg (19.84 lb)/10.3 kg (22.7 lb)

### Ordering Information

AX60501 (P/N: E260501109)	6-slot black shoesbox chassis for full-size SBC W/O PSU
AX60501 (P/N: E260501116)	6-slot beige shoesbox chassis for full-size SBC W/O PSU

\*Specifications and certifications are based on options and may vary.

### Power Supply Information

50904B24010E	ATX 400W FSP-400-70PFL (SK)
50916A06000E	ATX 600W SS-600ES2

### Backplane Options

#### PICMG 1.0

Models	Slots per Segment (ISA/PCI/PCIe/CPU)	Segment
ATX6022/6	1/4/0/1	Single


#### PICMG 1.3

Models	Slots per Segment (ISA/PCI/PCIe/CPU)	Segment
FAB105	0/3/1/1	Single
FAB109	0/0/4/1	Single
FAB110	0/2/2/1	Single
HAB206	0/3/1/1	Single

### Optional Accessories

50761222000E	LGA1151/1155/1156 CPU cooler
72061560000E	3.5" to 5.25" HDD bracket (Need to buy a pair)

Dimensions



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8 Industrial Chassis
- 9
- 10

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[AX60501WB-RC-NP W/O B/P,P/S W/USB](#)