

AX61135TM NEW

1U Expandability Rackmount Chassis for ATX Motherboard

Features

- Supports 12" x 9.6" standard ATX motherboard
- Two 4 cm system fan
- Supports 1U Flex ATX power supply
- Internal 2 x 3.5" HDD or internal 2 x 2.5" HDD



▲ Front view



▲ Rear view



▲ Top view

Specifications

Standard Color	Black
Construction	Heavy-duty steel
System Board	12" x 9.6" standard ATX motherboard
Drive Capacity	Internal 2 x 3.5" HDD or internal 2 x 2.5" HDD
Cooling	2 x 4 cm ball-bearing fan
Front Panel Indicators	1 x Power on/off 1 x HDD
Front Panel Controls	1 x Power on/off
Front Panel Connectors	2 x USB 2.0

Expansion Interface	1 x PCI (32-bit/33 MHz) or 1 x PCIe x16 slot via riser card
Operating Temperature	0°C to +40°C (+32°F to +104°F)
Dimensions	482 ± 1.0 mm (18.98") (W) x 471.50 ± 1.0 mm (18.48") (D) x 44 ± 1.0 mm (1.73") (H)
Weight (net/gross)	4.2 kg (9.26 lb)/6.7 kg (14.77 lb)

Ordering Information

AX61135TM (P/N: E261135100)	1U rackmount chassis for ATX motherboard w/o PSU
--------------------------------	--

Power Supply Information

50954724200E	ATX 300W FSP300-57FCB, L=750 mm
--------------	---------------------------------

Selection Guide


Model Name	Rear I/O	PCIe x16 to PCIe x16 riser card (P/N: 881611351A0E)	PCI to PCI riser card (P/N: 881611352A0E)
IMB530	72611351400E	○	○
IMB520(R)		○	X
IMB521(R)		○	X
IMB523(R)		○	○
IMB524(R)		○	○
IMB525(R)		○	○

○ : Support X: Not Support

Optional Accessories

881611352A0E	AX61135TM, PCI riser card (SLOT7) kit (E)
881611351A0E	AX61135TM, PCIe riser card (slot1 and 3) kit (E)
881611350A0E	Hot-swappable HDD tray set (Need to buy 594L3220B00E)
594L3220B00E	Hot-swappable HDD power cable
594G5208010E	SATA3 Cable 180D w/B.sleeve L=50cm
594G5208000E	SATA3 Cable 180D w/lock & B.sleeve L=50cm
59401210530E	Power cable 6 x 2 to 4P x 2/SATA x 2/AT x 8, L=65 cm
5076E510000E	LGA1151/LGA1200 CPU heatsink
59380703000E	COM Cable x2 w/BKT (,40), P=2.54 mm, L=300 mm
59380402010E	COM Cable x1 w/Bracket, P=2.54 mm, L=300 mm
59384500100E	SBC84500 Audio Cable w/BKT, P=2, L=420 mm
5938A808020E	USB Cable w/BKT USB x 2, 2 x 5 (10P-KEY) 400 mm

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Axiomtek:

[AX61135TM Hot-swappable HDD tray kit\(E\)](#) [AX61135TM-RC 1U Chassis w/o power](#) [AX61135TM PCI RISER Card](#)
[\(SLOT7\)SFP](#) [AX61135TM PCIE RISER \(SLOT1 and 3\)SFP](#) [AX61135TM_BK_IMB520](#) [AX61135TM_BK_IO_IMB500](#)