


# Actuator

45-  
2J31.25T0.000



<https://eao.com/p/45-2J31.25T0.000>

Your product:

---



## 45-2J31.25T0.000 Actuator

### FRONT

|                       |               |
|-----------------------|---------------|
| Front dimension:      | 58 mm x 35 mm |
| Front form:           | rectangular   |
| Front bezel colour:   | Silver        |
| Front bezel material: | Metal         |

### MOUNTING

|                   |                |
|-------------------|----------------|
| Design:           | raised         |
| Mounting cut-out: | Ø 22.3 mm      |
| Mounting type:    | Panel mounting |

### OPERATING-/INDICATION PART

|                    |                  |
|--------------------|------------------|
| Lens colour:       | Green-red        |
| Lens material:     | Plastic          |
| Lens illumination: | non illuminative |
| Lens shape:        | flush            |
| Lens optics:       | opaque           |

### MECHANICAL CHARACTERISTIC

|                      |                             |
|----------------------|-----------------------------|
| Switching action:    | Momentary                   |
| Switching system:    | Slow-make switching element |
| Mechanical lifetime: | 2 Mio. cycles of operation  |
| Operating frequency: | Max. 3 600/h                |

**Weight:** 0.068 kg

## **AMBIENT CONDITION**

**IP front protection:** IP66, IP67, IP69K

**Operating temperature:** – 25 °C ... + 70 °C

**Storage temperature:** – 40 °C ... + 80 °C

**Shock resistance:** According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

**Vibration resistance:** According to IEC 60068-2-6: 10 ... 500 Hz: 5 g

**Climate resistance:** During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6, 3B2

## **CERTIFICATE**

**REACH:** REACH compliant

**RoHS:** RoHS compliant


## **OTHER**

**Short Description:** Actuator, Ø 22.3 mm, 58 mm x 35 mm, flush, non illuminative, Green-red, Plastic, opaque, rectangular, Silver, Metal, Momentary, IP66, IP67, IP69K


**Housing colour:** Silver

**Housing material:** Metal


**Wiring diagrams:**




**Component layouts:**













#### Mounting cut-outs:



#### Dimension drawings:



## Where to Buy

|   | Distributor        | Quantity in Stock |     |   |
|---|--------------------|-------------------|-----|---|
|  | Mouser Electronics | 0 in stock        | Buy |  |
|  | Digi-Key           | 0 in stock        | Buy |  |
|  | Newark Electronics | 0 in stock        | Buy |  |
|  | RS Americas        | 0 in stock        | Buy |  |
|  | Sager              | 0 in stock        | Buy |  |

Powered by oemsecrets.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[45-2J31.25T0.000](#)