

# Actuator

61-  
2501.0/D



<https://eao.com/p/61-2501.0/D>

Your product:

---



## 61-2501.0/D Actuator

### MOUNTING

**Mounting type:** Panel mounting

### ELECTRICAL CHARACTERISTICS

**Electrostatic discharge (ESD):** 11 kV

### MECHANICAL CHARACTERISTIC

**Switching action:** Momentary - Rest (a) - Momentary

**Switching positions:** 3 positions

**Switching angle:** 42° left / 42° right

**Mechanical lifetime:** According to DIN/IEC 60512-5-6 and EN/IEC 60947-5-1, 50 000 cycles of operation

**Operating force:** 0.025...0.1 Nm snap-action switching element, 0.4 ... 0.16 Nm slow-make switching element

**Operating Travel:** ca. 2 x 42°

**Tightening torque:** Max. 0.5 Nm

**Weight:** 0.065 kg

### AMBIENT CONDITION

**IP Protection:** IP40 rear side, according to EN IEC 60529, IP67 front side, according to EN IEC 60529

**Operating temperature:** – 25 °C ... + 55 °C

**Storage temperature:** – 40 °C ... + 85 °C

### CERTIFICATE

**REACH:** REACH compliant


**RoHS:** RoHS compliant

## OTHER

**Short Description:** Actuator, Momentary - Rest (a) - Momentary

**Housing material:** Plastic, according to UL 94 V0, self-extinguishing


**Switching positions:**



**Wiring diagrams:**




**Mounting cut-outs:**




A = Solder/Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal




A = Solder/Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal




A = Solder/Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal



A = Solder/Plug-in terminal 2.8 mm x 0.5 mm


C = Screw terminal



A = Solder/Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal

### Dimension drawings:




A = Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal

E = Slow-make switching element

F = Snap-action switching element




A = Plug-in terminal 2.8 mm x 0.5 mm

C = Screw terminal









E = Slow-make switching element

F = Snap-action switching element



A = Plug-in terminal 2.8 mm x 0.5 mm  
 C = Screw terminal  
 E = Slow-make switching element  
 F = Snap-action switching element

## Where to Buy

Distributor		Quantity in Stock	
	RS Americas	15 in stock	<a href="#">Buy</a> 
	Digi-Key	8 in stock	<a href="#">Buy</a> 
	Mouser Electronics	0 in stock	<a href="#">Buy</a> 
	Newark Electronics	0 in stock	<a href="#">Buy</a> 

Powered by oemsecrets.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EAO:](#)

[61-2501.0/D](#)