




Specifications

CPU	LGA1155 for 3rd Gen Intel® Core™ i7/i5/i3 / Pentium® / Celeron® processors, up to 3.4GHz
System Memory	2x DDR3 DIMM Max. 16GB (Non-ECC)
System Chipset	MB961RF: Intel® Q67 PCH MB961F/MB961: Intel® H61 PCH
BIOS	AMI
Watchdog Timer	256 levels
SSD	N/A
H/W Monitor	Yes
Expansion Slots	1x PCI-E(x16), 1x PCI-E(x8) [PCI-E(x4) Link], 2x PCI
VGA Controller	3rd Gen Intel® Core™ i7/i5/i3/ Pentium®/ Celeron® Processor Integrated
VGA Memory	Max. shared memory - 1024 MB
Display Interface	Supports DVI-I, HDMI, 24 bit dual-channel LVDS (MB961RF/F)
LAN Controller	1x Intel® 82579V Gigabit LAN 1x Realtek RTL8111E Gigabit LAN
LAN Connector	RJ-45 on board
I/O Chipset	Fintek F81866AD-I 3x RS232, 1x RS232/422/485 (jumperless selection), LPT (MB961)
USB	2x USB 3.0 on board MB961F: 10x USB 2.0 (4 ports on board + 6 ports via pin header) MB961RF: 12x USB 2.0 (4 ports on board + 8 ports via pin header)
Serial ATA	MB961RF: 2x SATA II, 2 ports SATA III MB961F / MB961: 4x SATA II
Audio	Intel® H61/Q67 PCH built-in HD audio + Realtek ALC892 codec
Others	Digital I/O(4-in/4-out), iSMART, RAID (MB961RF only)
Dimensions	244mm x 244mm (9.6" x 9.6")
Max. Power Requirement	Intel® Core™ i7-3770 3.4GHz w/ 2x 4GB DDR3-1333 +12V: 0.25A; +5V: 2.21A; +5VSB: 0.12A; +3.3V: 1.46A
Operating Temperature	0°C~60°C (32°F~140°F)
Storage Temperature	-20°C~80°C (-4°F~176°F)
Relative Humidity	90% (non-condensing @60°C)


Features

- Supports 3rd Gen Intel® Core™ i7/i5/i3/Pentium®/ Celeron® processors, up to 3.4GHz
- 2x DDR3 DIMM, Max. 16GB
- Intel® processor integrated graphics, supports HDMI, DVI-I and LVDS (MB961RF/F)
- Intel® 82579V Gigabit LAN
- Realtek RTL8111E Gigabit LAN
- 12x USB 2.0, 2x USB 3.0, 4x COM, 2x SATA II, 2x SATA III
- 1x PCI-E(x16), 1x PCI-E(x8) [PCI-E(x4) Link], 2x PCI
- Watchdog timer, Digital I/O, iSMART
- Parallel port (MB961 only)

Ordering Information

MB961RF	LGA1155 Q67 Micro ATX motherboard with HDMI, DVI-I and LVDS, Dual Gigabit LAN, 2x SATA III, 2x SATA II, 1x PCI-E(x16), 1x PCI-E(x4), 2x PCI, RAID, iSMART
MB961F	LGA1155 H61 Micro ATX motherboard with HDMI, DVI-I and LVDS, Dual Gigabit LAN, 4x SATA II, 1x PCI-E(x16), 1x PCI-E(x4), 2x PCI, iSMART
MB961	LGA1155 H61 Micro ATX motherboard with LPT, Dual Gigabit LAN, 4x SATA II, 1x PCI-E(x16), 1x PCI-E(x4), 2x PCI, iSMART

Dimensions and Drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IBASE:](#)

[MB961F](#) [MB961RF](#)