



# RhinoJR® RJR110

## APPLICATIONS:

- Security
- Backup
- Testing
- Audio/Video Editing
- Drive Swapping
- Drive Transporting

## EASY INSTALLATION



Insert any capacity low-profile SATA, SCSI or PATA HDD in removable carriers



Install RhinoJR receiving frame into any standard 5.25" bay



Insert carrier into receiving frame & turn on powered key lock

## Reliable, Removable Storage Enclosure



- ▶ Supports Ultra320, SATA or PATA Drives\*
- ▶ Downward Compatible
- ▶ Hot Swappable
- ▶ Mounts into Any Half Height Bay

### Features

Anti-Static Device Protection

### Benefits

Reduces Risk of ESD Damage to Hard Drive

Carrier Locking Latch Mechanism

Provides Drive Security

Rugged All Metal Construction

Helps Protect Drives from Physical Damage

Exceeds Rotational Vibration Requirements

Supports Today's High-Speed Drives

\*Hard drive sold separately

# RhinoJR *RJR110*



## RJR110 68-pin U320

Part Number	Description
6650-1100-0500	Complete Assembly, 68-pin, U320, RoHS, Black
6651-1100-0500	Carrier Only, 68-pin, U320, RoHS, Black

## RJR110 80-pin U320

Part Number	Description
6650-2200-0500	Complete Assembly, 80-pin, U320, RoHS, Black
6651-2200-0500	Carrier Only, 80-pin, U320, RoHS, Black

## RJR110 ATA/133

Part Number	Description
6650-0000-0500	Complete Assembly, ATA/133, RoHS, Black
6651-0000-0500	Carrier Only, ATA/133, RoHS, Black

## RJR110 SATA 3Gb/s

Part Number	Description
6650-5000-0500	Complete Assembly, SATA 3Gb/s, RoHS, Black
6651-5000-0500	Carrier Only, SATA 3Gb/s, RoHS, Black

## Specifications:

- Carrier key lock/power switch provides additional security
- Anti-static device protection
- Drive activity indicator
- All metal construction
- Supports 3.5" low-profile drives
- Integrated cooling fan(s)
- Mounting hardware included
- 2 year warranty
- On SCSI Models:
  - Front panel unit ID indicator
  - Over temperature indicator
  - Fan status indicator
  - Reset switch



## Design:

	RJR110 68-Pin U320	RJR110 80-Pin U320	RJR110 ATA/133	RJR110 SATA 3Gb/s
<b>Weight</b>	2 Lbs. 4 oz	2 Lbs.	2 Lbs.	1 Lb. 13 oz
<b>Dimensions*</b> <b>(inches)</b>	Width - 5.75" Length - 8.98" Height - 1.65"	Width - 5.75" Length - 8.98" Height - 1.65"	Width - 5.75" Length - 8.98" Height - 1.65"	Width - 5.75" Length - 7.42" Height - 1.65"

\*Dimensions are for reference only

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[96RACK-5-ST-CU-B](#)