

PCI/ISA Backplanes


1U Butterfly Backplanes



Compatible with IPC Chassis: ACP-1010/ACP-1320

PCA-6103P2V-0A2E

- Segments: 1
- Slots: 2 PCI, 1 CPU
- PCI bus: 32-bit/33 MHz
- Size: 40 x 400 mm (1.57" x 15.75")
- Ordering Information: 989K610302E




2U Butterfly Backplanes



Compatible with IPC Chassis: ACP-2000/IPC-602


PCA-6105P4V-0B3E

- Segments: 1
- Slots: 4 PCI, 1 PICMG
- PCI bus: 32-bit/33 MHz
- Size: 80 x 260 mm (3.15" x 10.23")
- Ordering Information: 989K610511E



PCA-6106P3V-0B2E

- Segments: 1
- Slots: 1 ISA, 3 PCI, 2 PICMG
- PCI bus: 32-bit/33 MHz
- Size: 80 x 260 mm (3.15" x 10.23")
- Ordering Information: 989K610622E




5-slot PCI/ISA Backplanes



Compatible with IPC Chassis: IPC-6025

PCA-6105P3-5A1E

- Segments: 1
- Slots: 1 ISA, 2 PCI, 1 PICMG, 1 PCI/ISA
- Size: 106.5 mm x 327.66 mm (4.19" x 12.9")
- Ordering Information: PCA-6105P3-5A1E




6-slot PCI/ISA Backplanes



Compatible with IPC Chassis: IPC-6806/IPC-6606/IPC-6006


PCA-6106P4-0A2E

- Segments: 1
- Slots: 4 PCI, 2 PICMG
- Size: 142 x 270 mm (5.59" x 10.63")
- Ordering Information: PCA-6106P4-0A2E




PCA-6106P3-0D2E

- Segments: 1
- Slots: 2 ISA, 2 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 142 x 270 mm (5.59" x 10.63")
- Ordering Information: PCA-6106P3-0D2E



PCA-6106-0B2E

- Segments: 1
- Slots: 6 ISA
- Size: 142 x 175 mm (5.59" x 6.89")
- Ordering Information: PCA-6106-0B2E




8-slot PCI/ISA Backplanes



Compatible with IPC Chassis: IPC-6908/IPC-6608


PCA-6108P6-0B4E

- Segments: 1
- Slots: 1 ISA, 5 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 180 x 260 mm (7.09" x 10.24")
- PCI bridge: Tsi352-66CQY
- Primary PCI: 3 slots; Secondary PCI: 3 slots
- Ordering Information: PCA-6108P6-0B4E




PCA-6108P4-0C2E

- Segments: 1
- Slots: 3 ISA, 3 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 180 x 260 mm (7.09" x 10.24")
- Ordering Information: PCA-6108P4-0C2E




PCA-6108E-0C2E

- Segments: 1
- Slots: 8 ISA
- Size: 180 x 190 mm (7.09" x 7.48")
- Ordering Information: PCA-6108E-0C2E



PCA-6108-0B2E

- Segments: 1
- Slots: 8 ISA
- Size: 222 x 171 mm (8.74" x 6.73")
- Only for commercial PC chassis (baby AT size)
- Ordering Information: PCA-6108-0B2E



PCI/ISA Backplanes


14-slot PCI/ISA Backplanes



Compatible with IPC Chassis: ACP-4000, ACP-4010, ACP-4320, ACP-4360, IPC-510, IPC-610, IPC-611 and IPC-630


PCA-6114P12-0B3E

- Segments: 1
- Slots: 1 ISA, 11 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 315 x 300 mm (12.4" x 11.8")
- PCI bridge: Pericom PI7C8150BMAE
- Primary PCI: 3 slots;
Secondary PCI: 9 slots
- Ordering Information: PCA-6114P12-0B3E




PCA-6114P7-0D3E

- Segments: 1
- Slots: 4 ISA, 6 PCI, 3 PICMG, 1 PCI/ISA
- Size: 315 x 260 mm (12.4" x 10.24")
- PCI bridge: Tsi352-66CQY
- Primary PCI: 3 slots; Secondary PCI: 4 slots
- Ordering Information: PCA-6114P7-0D3E




PCA-6114P4-0C2E

- Segments: 1
- Slots: 8 ISA, 4 PCI, 2 PICMG
- Size: 315 x 260 mm (12.4" x 10.24")
- Ordering Information: PCA-6114P4-0C2E
- When choosing to install in ACP-4320, 4360 and IPC-510 chassis, 1U cooler is required



PCA-6113P4R-0C2E

- Segments: 1
- Slots: 7 ISA, 4 PCI, 2 PICMG
- Size: 315 x 260 mm (12.4" x 10.24")
- Ordering Information: PCA-6113P4R-0C2E




PCA-6115-0B2E

- Segments: 1
- Slots: 15 ISA
- Size: 326 x 190 mm (12.83" x 7.48")
- Compatible with IPC-615
- Ordering Information: PCA-6115-0B2E




PCA-6114-0B2E

- Segments: 1
- Slots: 14 ISA
- Size: 315 x 175 mm (12.4" x 6.89")
- Ordering Information: PCA-6114-0B2E




PCA-6114P10-0B2E

- Segments: 1
- Slots: 2 ISA, 10 PCI, 2 PICMG
- Size: 315 x 260 mm (12.4" x 10.24")
- PCI bridge: Pericom PI7C8150BMAE
- Primary PCI: 3 slots;
Secondary PCI: 7 slots
- Ordering Information: PCA-6114P10-0B2E



PCA-6113DP4-0A2E

- Segments: 2
- Slots: 2 ISA, 7 PCI, 1 PICMG/
PCI, 3 PICMG
- Size: 315 x 260 mm (12.4" x 10.24")
- Ordering Information: PCA-6113DP4-0A2E
- Compatible with IPC Chassis: Only for ACP-4010.




20-slot PCI/ISA Backplanes



Compatible with IPC Chassis : IPC-623, IPC-622, ACP-7360, ACP-5360


PCA-6120DP4-OB2E

- Segments: 2
- Slots: 7 ISA, 6 PCI, 2 PICMG/PCI, 4 PICMG
- Size: 420 x 260 mm (16.42" x 10.24")
- Ordering Information: PCA-6120DP4-OB2E




PCA-6116QP2-OB2E

- Segments: 4
- Slots: 1 ISA, 8 PCI, 7 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- Ordering Information: PCA-6116QP2-OB2E




PCA-6120P18-0A2E

- Segments: 1
- Slots: 1 ISA, 17 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- PCI bridge: Three Pericom PI7C8150BMAE
- Secondary: 6 slot/6 slot/6 slot
- Ordering Information: PCA-6120P18-0A2E




PCA-6119P17-0B2E

- Segments: 1
- Slots: 16 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- PCI bridge: Dual Pericom PI7C8150BMAE
- Primary PCI: 2 slots; Secondary PCI: 8 slots + 7 slots
- Ordering Information: PCA-6119P17-0B2E




PCA-6119P7-0B3E

- Segments: 1
- Slots: 10 ISA, 7 PCI, 2 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- PCI bridge: Tsi352-66CQY
- Primary PCI: 3 slots; Secondary PCI: 4 slots
- Ordering Information: PCA-6119P7-0B3E




PCA-6120P12-0A2E

- Segments: 1
- Slots: 7 ISA, 11 PCI, 1 PICMG/PCI, 1 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- PCI bridge: Pericom PI7C8150BMAE
- Primary PCI: 3 slots; Secondary PCI: 9 slots
- Ordering Information: PCA-6120P12-0A2E




PCA-6120P4-0B2E

- Segment: 1
- Slots: 14 ISA, 4 PCI, 2 PICMG
- Size: 417 x 260 mm (16.42" x 10.24")
- Ordering Information: PCA-6120P4-0B2E



PCA-6120Q-0B2E

- Segment: 4
- Slots: 5-5-5-5 ISA
- Size: 417 x 200 mm (16.42" x 7.87")
- Ordering Information: PCA-6120Q-0B2E



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[989K610302E](#)