

MINIATURE BULKHEAD JACKS 70/370 SERIES, TRB/TRT

BJ377 Shown BULKHEAD JACK FRONT MOUNT, SOLDER POT 3-lug BJ770 Ground tab BJ770GL 2-lug BJ77TL 4-lug BJ77FL Threaded BJ377 (Hermetically sealed version available, pg.13) Mounting Hole: D4.125	BJ79C Shown BULKHEAD CABLE JACK TOOL CRIMP 3-lug BJ79C-1 2-lug BJ79CTL-1 4-lug BJ79CFL-1 Threaded BJ379C-1 For polarizations, contact the factory. Mounting Hole: D3.109
BJ378 Shown FEED-THRU BULKHEAD JACK Threaded 3-lug BJ78 2-lug BJ78TL 4-lug BJ78FL Threaded BJ378 (Hermetically sealed version available, pg.13) Mounting Hole: D3.187	BJ379-7 Shown BULKHEAD CABLE JACK WRENCH CRIMP 3-lug BJ79-1 2-lug BJ79TL-1 4-lug BJ79FL-1 Threaded BJ379-1 Mounting Hole: D3.160
BJ76 Shown BULKHEAD JACK REAR MOUNT, SOLDER POT 3-lug BJ76 2-lug BJ76TL 4-lug BJ76FL Threaded BJ376* Mounting Holes: D3.240 w/o solder lug/D3.208 w/ solder lug (* Hermetically sealed version avail. pg.13)	BJ75 Shown INSULATED BULKHEAD JACK REAR MOUNT, SOLDER POT 3-lug BJ75 2-lug BJ75TL 4-lug BJ75FL Threaded BJ375 Mounting Hole: D2.140
BJ74-9 Shown INSULATED BULKHEAD CABLE JACK WRENCH CRIMP 3-lug BJ74-1 2-lug BJ74TL-1 4-lug BJ74FL-1 Threaded BJ374-1 Mounting Hole: D2.140	BJ74C-202 Shown INSULATED BULKHEAD CABLE JACK TOOL CRIMP 3-lug BJ74C-1 2-lug BJ74CTL-1 4-lug BJ74CFL-1 Threaded BJ374C-1 Mounting Hole: D2.140
BJ73 Shown INSULATED FEED-THRU JACK 3-lug BJ73 2-lug BJ73TL 4-lug BJ73FL Threaded BJ373 Mounting Hole: D2.140	BJ72 Shown INSULATED BULKHEAD JACK FRONT MOUNT 3-lug BJ72 2-lug BJ72TL 4-lug BJ72FL Threaded BJ372 Mounting Hole: D2.140

△ - See cable group table on pages 68-88. "D" mounting holes see page 45. For polarizations, contact the factory.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[BJ79TL-32](#)