







RED INDICATES ORIGINAL

DASH NO	FIG	CABLES ACCOMMODATED	A DIM	B FLATS	C HEX	ASSEMBLE PER
-1		RG-58				
-U1		ESSEX 621-715				
-2		RG-59				
-U2		BELDEN 8279				
-2A		AT&T 730A				
-U2A		RG-223				
-2B		RG-55	.931	.437	.437	TAI-101
-3		RG-122				
-U3		BELDEN 8218				
-3A		RG-174				
-4		RG-187				
-U4		RG-196				
-5		HEWLETT-PACKARD 8120-1107				
-U5		BELDEN 9231	.988	.500	.500	TAI-119
-5A		RG-5				
-U5A		RG-6				
-5B		RG-303				
-U5B		RG-180				
-6		GRUMMAN GC875GPI				
-U6		RG-187 DBL SHLD				
-6E		BELDEN 8228	.931	.437	.437	TAI-101
-U6E		275-3991 MICRODOT				
-7		616-569 AMPEX				
-U7		810 RAYCHEM				
-8		RG-304				
-U8		9248 BELDEN				
-9		BRAND-REX B749				
-U9		GORE C06C032				
-10		88281 BELDEN	.988	.500	.500	TAI-119
-U10		89120 BELDEN				
-11		89555 BELDEN				
-U11		734A, AT&T	.931	.437	.437	TAI-101
-12		RG-405				
-U12		RG-402				TAI-130



REV	ECO NO.	DESCRIPTION	DWN	APPROVED	DATE
AE	11583	DASH NO COLUMN, -U1 WAS -10; SHEET 2, MADE CORRECTION IN 1. SECTION VIEW, SEE ECO	LSR	[Signature]	4/26/90



INCH	MM
.005	0.13
.030	0.76
.096	2.44
.125	3.18
.250	6.35
.312	7.92
.350	8.89
.437	11.10
.500	12.70
.606	15.39
.931	23.65
.988	25.10
1.846	46.89

IF BEND RELIEF SPRING REQUIRED ADD SUFFIX "BR" TO MODEL NO. (SEE FIG 3). (NOT AVAILABLE WITH CABLE GROUPS -6, -U6, -6E, -U6E, -51, -U51, -52, -U52, -63, -U63 -086, -U086, -141 & -U141)

FOR CABLE GROUPS -1 & -U1 SUPPLY 1 EA ACA1 FOR CABLE GROUPS -2 & -U2 SUPPLY 1 EA ACA2 FOR CABLE GROUPS -5 & -U5 SUPPLY 1 EA ACA5 MAY BE ASSEMBLED TO CABLE/CONNECTOR ASSY USING 3M SCOTCHGRIP NO. 1099 PLASTIC ADHESIVE, OR EQUIV.

IF PLASTIC STRAIN RELIEF REQUIRED, ADD SUFFIX "BT" TO MODEL NO. (ONLY AVAILABLE WITH -1, -U1, -2, -U2, -5, -U5)

4. BNC COAXIAL CABLE PLUG BOTH 50 & 75 OHM VERSIONS
3. DASH NO DENOTES CABLE GROUP EXCEPT "U" PREFIX DENOTES 75 OHM VERSION
2. FINISH: TFS-1A(NICKEL)(TOTAL BUILD-UP .000180-.000450)
1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
12-09	105-1004	1-0204	110-0002
105-0717	105-0870	1-0207	1-0227
305-0541	105-0698	1-0212	105-0944
105-0158	105-0697	1-0215	105-0007
305-0383	105-0659	1-0216	105-0449
305-0187	105-0461	1-0218	105-0394
105-1016	105-0295	1-0220	1-0304
NEXT ASSY		APPR	4/26/90
		SCALE	4/1
		DATE	10-22-73
		SHEET	1C

TROMPETER
BY CONRAD

PL20/BR/
UPL20/BR

14949

1-0369

AE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PL20-5A](#)