

# RED INDICATES ORIGINAL

DWG  
SIZE  
C

DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR REPRODUCTION OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS

310-0056


SH 1

REV	EO	DESCRIPTION	DWN	APPROVED	DATE
N	12087	-306 TAI-218 WAS TAI-168; ADDED -308 & -309; SEE ECO	DKC	WJM	8/26/97

DASH NO	CABLES ACCOMMODATED	A HEX	B DIM	C MAX	ASSEMBLE PER
-201	M17/176-00002	.344	.030	1.70	TAI-168
-202	TVC-78-1				
-203	TVC-124-1A				
-204	10602, RAYCHEM				
-205	TWAC-78-1F2				
-206	782600130, RAYCHEM				
-207	83310, BELDEN				
-208	202-3927, MICRODOT				
-209	202-3942, MICRODOT				
-210	B451, BELDEN				
-211	202-3934, MICRODOT				
-212	2524E0114, RAYCHEM				
-213	TVC-78-2				
-214	TVC-124-2				
-215	BL982, TIMES				
-216	BL1242, TIMES				
-217	GC875TM24H, GRUMMAN	.344	.030	1.44	TAI-138
-218	EDP221888, RAYCHEM				
-219	252801114, RAYCHEM				
-220	GC875RR1, GRUMMAN				
-221	10614, RAYCHEM				
-222	10613, RAYCHEM				
-223	HMS2-1149, HUGHES				
-224					
-225					
-226					

DASH NO	CABLES ACCOMMODATED	A HEX	B DIM	C MAX	ASSEMBLE PER
-301	GC875GC1, GRUMMAN	.344	.030	1.80	TAI-168
-302	GC875GB1, GRUMMAN				
-303	7528A5314, RAYCHEM				
-304					
-305	M17/177-00001, THERMATICS				TAI-218
-306	TRC-50-2				
-307	M17/134-00002				TAI-168
-308	TRC-75-1				
-309	TRC-75-2				TAI-218
-310	TRC-50-1				

INCH	MM
.005	0.13
.030	0.76
.344	8.74
.593	15.06
1.00	25.40
1.25	31.75
1.297	32.94
1.44	36.58
1.70	43.18
1.75	44.45



5. EXAMPLE OF COMPLETE MODEL NO:  
PL75CFL-201

BASIC MODEL NO. CABLE GROUP  
DASH NO.

1 SHRINKABLE STRAIN RELIEF AND/OR SHRINKABLE SEALING SLEEVE SUPPLIED LOOSE AS FOLLOWS:

- CABLE GROUPS -201 THROUGH -210, -217 THROUGH -303, -305, -307 & -309  
1 SHRINKABLE STRAIN RELIEF (1.00 LONG)  
1 SHRINKABLE SEALING SLEEVE (1.25 LONG)
- CABLE GROUPS -211 THROUGH -216, -306 & -308  
1 SHRINKABLE STRAIN RELIEF (1.75 LONG)

3. 4-LUG BAYONET CONCENTRIC TWINAX/TRIAX TR8 FULL CRIMP CABLE PLUG

2. FINISH: TFS-1A (NICKEL)

1. ALL DIMENSIONS ARE IN INCHES



-202 SHOWN

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL. UNLESS SPECIFIED .XX ± .XXX ±.005 .0000 ±.0002 ANGLES	<b>TROMPETER</b> RF connectivity	PL75CFL	
DWN DKC 8-4-97	MATERIAL CODE IDENT	DRAWING NO.	REV
CHK WJM 8-20-97	14949	310-0056	N
ENGR	APPR	SCALE 4/1	DATE 10/4/85 SHEET 1 OF 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PL75CFL-204](#) [BJ79TL-25A](#)