

## Modular Connectors

Cinch Connectivity Solutions presents its premium line of USA made modular connectors which are designed to meet the strict demands of high speed analog and digital signals.

These modular plugs are available in 4, 6, 8 and 10 pin versions and contacts are plated with 50 micro-inches of gold for better conductivity and data assurance. This allows data to flow up to Category 6 speeds.

These connectors consist of a patented design allowing termination of one connector for either solid or stranded cable, and are available in different styles to terminate round or flat cable types. The RJ45 plugs are available in shielded and unshielded versions, as well as for use on bonded or non-bonded cable.

These modular plugs are ideal for use in Networking, Digital Video, TV Broadcast, Aircraft, Test Instruments and Medical Imaging Equipment applications. We also provide a plug that terminates 22AWG wire as used by the Automotive Industry.



### Features

- 50 Micro-inch Gold plated contacts
- Maximum contact resistance 10mΩ Max
- Terminate to Stranded or Solid conductors
- For both Round and Flat cable
- UL listed & Certified
- Made in USA
- Easy installation with most crimp tools

**Cinch Connectivity Solutions also offers a complete selection of commonly used Ratchet and Non-Ratchet Modular Plug Crimping tools. See below for a list for tool part numbers and a list of available Modular Plugs.**

Part Number	Description	Suggested Tool
32-2098UL	RJ45 (8P8C), Straight, Shielded, Round Cable	1, 2, 3
32-2198UL	RJ45 (8P8C), Offset w/ Load Bar, Unshielded, Round Cable	1, 2, 3
32-2298UL	RJ45UL (8P8C), Shielded, Straight, Round Cable, CAT5E	1, 2, 3
32-5910UL	RJ45 (10P10C), Straight, Unshielded, Round Cable	1, 2, 3
32-5954UL	RJ11 (6P4C), Straight, Unshielded, Flat Cable	1, 2, 3
32-5956UL	RJ12 (6P6C), Straight, Unshielded, Flat Cable	1, 2, 3
32-5958UL	RJ45 (8P8C), Straight, Unshielded, Flat Cable	1, 2, 3
32-5964UL	RJ22 (4P4C), Straight, Unshielded, Flat or Round (Handset Plug)	3
32-5994UL	RJ11 (6P4C), Straight, Unshielded, Round Cable	1, 2, 3
32-5996UL	RJ12 (6P6C), Straight, Unshielded, Round Cable	1, 2, 3
32-5998EUL	RJ45 (8P8C), CAT5E, Offset, Unshielded, Round Cable	1, 2, 3
32-5998UL	RJ45 (8P8C), Straight, Unshielded, Round Cable	1, 2, 3
32-6198UL	RJ45 (8P8C), CAT6, Offset w/ Load Bar, Unshielded, Round Cable	1, 2, 3

P=Position, C=Conductor

Part Number	Terminate	Tool Type
1 24-4680P	4, 6, 8 & 8 Keyed (works with AMP & Stewart Plugs)	Non-Ratchet
2 24-4681P	2, 4, 6, 8 & 8 Keyed	Non-Ratchet
3 24-7865P	2, 4, 6, 8, 8 Keyed & 10 (works with DEC 4/6 and 4C Handset Plugs)	Ratchet
4 24-7748P	All 8P8C Keyed Modular Plugs	Non-Ratchet



**Asia Pacific**  
+86 21 5442 7668  
ccs.asia.sales@as.cinch.com

**Europe, Middle East & Africa**  
+44 (0) 1245 342060  
CinchConnectivity@eu.cinch.com

**North America**  
+1 507.833.8822  
ccsorders@us.cinch.com

[belfuse.com/cinch](http://belfuse.com/cinch)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[30-3007-3](#)