







RED INDICATES ORIGINAL

DASH NO	FIG	CABLES ACCOMMODATED	A DIM	B FLATS	C HEX	ASSEMBLE PER
-1		RG-58				
-U1		ESSEX 621-715				
-2		RG-59				
-U2		BELDEN 8279				
-2A		AT&T 730A				
-U2A		RG-223				
-2B		RG-55	.931	.437	.437	TAI-101
-3		RG-122				
-U3		BELDEN 8218				
-3A		RG-174				
-4		RG-187				
-U4		RG-196				
-5		HEWLETT-PACKARD 8120-1107				
-U5		BELDEN 9231	.988	.500	.500	TAI-119
-5A		RG-5				
-U5A		RG-6				
-5B		RG-303				
-U5B		RG-180				
-6		GRUMMAN GC875GPI				
-U6		RG-187 DBL SHLD				
-6E		BELDEN 8228	.931	.437	.437	TAI-101
-U6E		275-3991 MICRODOT				
-7		616-569 AMPEX				
-U7		810 RAYCHEM				
-8		RG-304				
-U8		9248 BELDEN				
-9		BRAND-REX B749				
-U9		GORE C06C032				
-10		88281 BELDEN	.988	.500	.500	TAI-119
-U10		89120 BELDEN				
-11		89555 BELDEN				
-U11		734A, AT&T	.931	.437	.437	TAI-101
-12		RG-405				
-U12		RG-402				TAI-130



REV	ECO NO.	DESCRIPTION	DWN	APPROVED	DATE
AE	11583	DASH NO COLUMN, -U1 WAS -10; SHEET 2, MADE CORRECTION IN 1. SECTION VIEW, SEE ECO	LSR	[Signature]	4/26/73



INCH	MM
.005	0.13
.030	0.76
.096	2.44
.125	3.18
.250	6.35
.312	7.92
.350	8.89
.437	11.10
.500	12.70
.606	15.39
.931	23.65
.988	25.10
1.846	46.89

△ IF BEND RELIEF SPRING REQUIRED ADD SUFFIX "BR" TO MODEL NO. (SEE FIG 3). (NOT AVAILABLE WITH CABLE GROUPS -6, -U6, -6E, -U6E, -51, -U51, -52, -U52, -63, -U63 -086, -U086, -141 & -U141)

△ FOR CABLE GROUPS -1 & -U1 SUPPLY 1 EA ACA1 FOR CABLE GROUPS -2 & -U2 SUPPLY 1 EA ACA2 FOR CABLE GROUPS -5 & -U5 SUPPLY 1 EA ACA5 MAY BE ASSEMBLED TO CABLE/CONNECTOR ASSY USING 3M SCOTCHGRIP NO. 1099 PLASTIC ADHESIVE, OR EQUIV.

△ IF PLASTIC STRAIN RELIEF REQUIRED, ADD SUFFIX "BT" TO MODEL NO. (ONLY AVAILABLE WITH -1, -U1, -2, -U2, -5, -U5)

4. BNC COAXIAL CABLE PLUG BOTH 50 & 75 OHM VERSIONS
3. DASH NO DENOTES CABLE GROUP EXCEPT "U" PREFIX DENOTES 75 OHM VERSION
2. FINISH: TFS-1A(NICKEL)(TOTAL BUILD-UP .000180-.000450)
1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
12-09	105-1004	1-0204	110-0002
105-0717	105-0870	1-0207	1-0227
305-0541	105-0698	1-0212	105-0944
105-0158	105-0697	1-0215	105-0007
305-0383	105-0659	1-0216	105-0449
305-0187	105-0461	1-0218	105-0394
105-1016	105-0295	1-0220	1-0304
NEXT ASSY			
APPR [Signature]		DATE 4/26/73	SCALE 4/1
MATERIAL		CODE IDENT 14949	DRAWING NO. I-0369
CHK [Signature]		ENG [Signature]	AE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PL20-2](#)