

RED IS ORIGINAL

TABLE 1			TABLE 2					REVISIONS				310-0069	SH 1	
DASH NO	MODEL NO	CENTER CONTACT/ INTMD CONTACT TYPE	CABLE GROUP NO	CABLES ACCOMMODATED	A HEX	B MAX	C DIM	ASSEMBLE PER	REV	EO	DESCRIPTION	DWN	APPROVED	DATE
-1	PLR3455ACP	SOCKET/PIN	-201	M17/176-00002					E	10055	SH1: PICTORIALY REVISED SEALING SLEEVE; GENERAL UPDATE SH2: SEE ECO	DKG	12/4/92	
-2	PLR3455ACS	PIN/SOCKET	-202	TWC-78-1, TROMPETER										
			-203	TWC-124-1A, TROMPETER										
			-204	10502, RAYCHEM										
			-205	TWAC-78-1F2, TROMPETER										
			-206	782600130, RAYCHEM										
			-208	202-3927, MICRODOT	.255	1.50	1.43	TA1-170						
			-209	202-3942, MICRODOT										
			-212	2524E0114, RAYCHEM										
			-217	9CB75TM24H, GRUMMAN										
			-218	EP022188B, RAYCHEM										
			-219	2526D1114, RAYCHEM										
			-220	9CB75SR1, GRUMMAN										
			-221	10614, RAYCHEM										
			-222	10613, RAYCHEM										
			-223	HMS2-1149, HUGHES										
			-303	10598, RAYCHEM	.344	1.88	1.49	TA1-186						

INCH	MM
.005	0.13
.03	0.76
.045	1.14
.255	6.48
.450	11.43
1.10	27.94
1.25	31.75
1.43	36.32

RECOMMENDED
HEX CRIMP

.450 DIA MAX
OVER KNURL

5. EXAMPLE OF COMPLETE MODEL NO:

PLR3455AC P - 201

BASIC MODEL NO (SEE TABLE 1) CABLE GROUP NO (SEE TABLE 2)

CENTER CONTACT/INTERMEDIATE CONTACT TYPE (SEE TABLE 1)

4. EXAMPLE OF COMPLETE PART NO:

310-0069 - 1 - 201

BASIC PART NO DASH NO CENTER CONTACT/INTERMEDIATE CONTACT TYPE (SEE TABLE 1) CABLE GROUP NO (SEE TABLE 2)

3. CONCENTRIC TWINAX 4 PIECE ASSY, RIGHT ANGLE FULL CRIMP CABLE PLUG, SOCKET CENTER CONTACT AND PIN INTERMEDIATE CONTACT OR PIN CENTER CONTACT AND SOCKET INTERMEDIATE CONTACT

2. FINISH: TFS-1U (500 HR SALT SPRAY), NICKEL

1. ALL DIM ARE IN INCHES

-1 -201 SHOWN

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED XX ± .03 XXX ± .005 XXXX ANGLES	TROMPETER RF connectivity	PLR3455AC/P/S	
DWN DKG 12/2/92	MATERIAL	CODE IDENT 14949	DRAWING NO. 310-0069
CHK 12/3/92	ENGR	DATE 11/4/88	SHEET 1 OF 2
NEXT ASSY	APPR 12/3/92	SCALE 2/1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PLR3455ACS-222](#)