

Specification Sheet

Part Number: 151-00834

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.



Connector Clip with Oval Fir Tree, 6.2x12.2mm Hole Dia, PA66HIRHS, Black, 10,000/box

Article Number	151-00834
----------------	-----------

Type	YCCKSFT62x122PT1.7-2.3 90°
------	----------------------------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Connector Clip with Oval Fir Tree, 6.2x12.2mm Hole Dia, PA66HIRHS, Black, 10,000/box
-------------------	--

Global Part Name	YCCKSFT62x122PT1.7-2.3 90°-PA66HIRHS-BK
Length L (Metric)	27.0
Fixation Method	Fir Tree for oval holes
Width W (Metric)	21.0
Height H (Metric)	12.1
Panel Thickness Min (Imperial)	0.07
Panel Thickness Max (Imperial)	0.09
Panel Thickness Min (Metric)	1.7
Panel Thickness Max (Metric)	2.3
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 "
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.24
Mounting Hole Diameter D Max (Metric)	6.2
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)

Material Shortcut	PA66HIRHS
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10000
Package Quantity (Metric)	10000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00834](#)