

Specification Sheet

Part Number: 156-02882



- MOC stud mount secures bundles above a bolt or stud.
- Patented retention design features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement.
- Controlled flex and angled entry promote easy installation.
- Independent rotation allows for adjustable routing orientation.
- High-performance stud mount design allows for easy installation and delivers outstanding stud retention to keep bundles secure.

Stud Mount to MOC Clip, 16mm Clip Above Mount, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02882
Type	SMFMOC16M
Color	Black (BK)
Quantity Per	bag
Product Description	The MOC with stud mount features HellermannTyton's unique retention clip with a best-in-class stud mount to secure to a 5mm or 6mm stud or bolt. The mount delivers a low insertion force while exhibiting high extraction resistance for a secure mounting point.

Short Description	Stud Mount to MOC Clip, 16mm Clip Above Mount, 5mm/6mm Stud Mount, PA66HIRHSUV, Black, 2000/ctn
Global Part Name	SMFMOC16M-PA66HIRHSUV-BK
Length L (Imperial)	1.02
Length L (Metric)	25.8
Fixation Method	Stud Mount
Bundle Diameter Min (Imperial)	0.55
Bundle Diameter Min (Metric)	14.0
Bundle Diameter Max (Imperial)	0.72
Bundle Diameter Max (Metric)	18.3
Height H (Imperial)	1.73
Height H (Metric)	44.0
Depth D (Imperial)	0.59
Depth D (Metric)	15.0
Nominal Diameter (Metric)	16.0
Stud Diameter (Metric)	5.0 mm 6.0 mm
Stud Diamater (Imperial)	0.20 ";0.24

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02882](#)