


Specification Sheet

Part Number: 118-00032

Extreme temperature range for excellent performance in a range of environments.

Low-profile, contoured head takes up less space and protects sensitive wires.

Delivers the performance of a metal tie with the ease of use of plastic.



Article Number	118-00032
----------------	-----------

Type	PT2A
------	------

Color	Beige (BGE)
-------	-------------

Quantity Per	bag
--------------	-----

Product Description	PEEK Ties withstand temperatures from -67 to 464 degrees F and provide excellent resistance to chemicals, acids, radiation and abrasion. The low-profile, contoured head takes up less space and protects sensitive wires running adjacent to it.
---------------------	---

Short Description	High-Temp Cable Tie, 5.7" Long, 52lb Tensile Strength, PEEK, Beige, 100/pkg
-------------------	---

Global Part Name	PT2A-PEEK-BGE
------------------	---------------

Minimum Tensile Strength (Imperial)	52
Minimum Tensile Strength (Metric)	230
Length L (Imperial)	5.7
Length L (Metric)	145.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.13
Width W (Metric)	3.4
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.2

Cable Tie Head Length (Imperial)	0.22
Cable Tie Head Width (Imperial)	0.24
Material	Polyetheretherketone (PEEK)
Material Shortcut	PEEK
Flammability	UL 94 V-0 (3 mm)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-67°F to +464°F (-55°C to +240°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	IEC EN 62275 Lloyd's Register IEC 62275 DNV GL EN 62275:2009
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[118-00032](#)