


Specification Sheet

Part Number: 118-00116

Extreme temperature range for excellent performance in a range of environments.

Low-profile, contoured head takes up less space and protects sensitive wires.

Delivers the performance of a metal tie with the ease of use of plastic.



High-Temp Cable Tie, 9.8" Long, 67lb Tensile Strength, PEEK, Beige, 100/pkg

Article Number	118-00116
----------------	-----------

Type	PT3B
------	------

Color	Beige (BGE)
-------	-------------

Quantity Per	bag
--------------	-----

Product Description	PEEK Ties withstand temperatures from -67 to 464° F and provide excellent resistance to chemicals, acids, radiation and abrasion. The low-profile, contoured head takes up less space and protects sensitive wires running adjacent to it.
---------------------	--

Short Description	High-Temp Cable Tie, 9.8" Long, 67lb Tensile Strength, PEEK, Beige, 100/pkg
-------------------	---

Global Part Name	PT3B-PEEK-BGE
------------------	---------------

Minimum Tensile Strength (Imperial)	67.0
Minimum Tensile Strength (Metric)	300
Length L (Imperial)	9.8
Length L (Metric)	250.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.65
Bundle Diameter Min (Imperial)	0.16
Bundle Diameter Min (Metric)	4.0
Bundle Diameter Max (Imperial)	2.6
Bundle Diameter Max (Metric)	65.0
Thickness T (Metric)	1.5

Material	Polyetheretherketone (PEEK)
Material Shortcut	PEEK
Flammability	UL 94 V-0 (3 mm)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-67°F to +464°F (-55°C to +240°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[118-00116](#)