


Specification Sheet

Part Number: 151-00651



The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters.

Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box

Article Number	151-00651
----------------	-----------

Type	TC6FT6LG
------	----------

Color	Natural (NA)
-------	--------------

Quantity Per	box
--------------	-----

Product Description	HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.
---------------------	---

Short Description	Bundling Clip with Fir Tree, 1.5" Long, 0.7 - 18.0mm Panel Thickness, PA66HIRHS, Natural, 2000/box
-------------------	--

Global Part Name	TC6FT6LG-PA66HIRHS-NA
------------------	-----------------------

Length L (Imperial)	1.5
Length L (Metric)	38.1
Fixation Method	Fir Tree
Width W (Imperial)	0.5
Width W (Metric)	12.0
Height H (Imperial)	1.0
Height H (Metric)	26.60
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.71
Panel Thickness Min (Metric)	0.7
Panel Thickness Max (Metric)	18.0
Mounting Hole Diameter D (Imperial)	0.24 - 0.27
Mounting Hole Diameter D (Metric)	6.2 - 6.8 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.8

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-00651](#)