

Specification Sheet

Part Number: 151-01404

HellermannTyton connector clips provide a simple and easy method for mounting connectors to a mounting surface in a variety of applications. Detailed designs include anti-rattle disc features, anti-rotation oval fir trees, and clamps for mounting on edges.

HellermannTyton offers an assortment of connector clips that are available for a variety of connector slot designs found on most of the largest global connector manufacturers.



Connector Clip with Bracket, 2.79" Long, PA66HIRHS, Natural, 800/box

|                     |                                                                                                                                                                                                                                                                                                                               |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 151-01404                                                                                                                                                                                                                                                                                                                     |
| Type                | BCBRKT55M                                                                                                                                                                                                                                                                                                                     |
| Color               | Natural (NA)                                                                                                                                                                                                                                                                                                                  |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                                                        |
| Product Description | HellermannTyton connector clips, for oval holes, are mounted simply by pushing them onto the corresponding clip. The clips provide a wide range of mounting options with anti-rattle and anti-rotation features. The fir tree locks into place when inserted into the hole palpably and ensures a secure fixing at all times. |
| Short Description   | Connector Clip with Bracket, 2.79" Long, PA66HIRHS, Natural, 800/box                                                                                                                                                                                                                                                          |

|                                     |                                                                  |
|-------------------------------------|------------------------------------------------------------------|
| <b>Global Part Name</b>             | BCBRKT55M-PA66HIRHS-NA                                           |
| <b>Length L (Imperial)</b>          | 2.79                                                             |
| <b>Length L (Metric)</b>            | 70.9                                                             |
| <b>Offset Length (Imperial)</b>     | 2.17                                                             |
| <b>Offset Length (Metric)</b>       | 55.15                                                            |
| <b>Width W (Imperial)</b>           | 1.97                                                             |
| <b>Width W (Metric)</b>             | 50.0                                                             |
| <b>Height H (Imperial)</b>          | 0.62                                                             |
| <b>Height H (Metric)</b>            | 15.8                                                             |
| <b>Material</b>                     | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| <b>Material Shortcut</b>            | PA66HIRHS                                                        |
| <b>Operating Temperature</b>        | -40°F to +230°F (-40°C to +110°C)                                |
| <b>Reach Compliant (Article 33)</b> | Yes                                                              |
| <b>ROHS Compliant</b>               | Yes                                                              |

|                                    |      |
|------------------------------------|------|
| <b>Package Quantity (Imperial)</b> | 3000 |
|------------------------------------|------|

|                                  |      |
|----------------------------------|------|
| <b>Package Quantity (Metric)</b> | 3000 |
|----------------------------------|------|

|                       |            |
|-----------------------|------------|
| <b>Customs Number</b> | 3926909988 |
|-----------------------|------------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[151-01404](#)