

Specification Sheet

Part Number: 170-03190



A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.

Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.

Cuts with ordinary scissors for fast, easy application.

|                     |                                                                                                                                                                                                                                                                                                |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 170-03190                                                                                                                                                                                                                                                                                      |
| Type                | BSHTTSW14SB                                                                                                                                                                                                                                                                                    |
| Color               | Silver (SR)                                                                                                                                                                                                                                                                                    |
| Quantity Per        | box                                                                                                                                                                                                                                                                                            |
| Product Description | Aluminum Laminated Fiberglass Wrap sleeving combines the protection of bonded aluminum and fiberglass into a robust solution that deflects radiant heat away from sensitive wires and cables. Wrap-around design allows for fast and easy installation and maintenance. Sold in 4-foot sticks. |
| Short Description   | Braided Wrap, Aluminum Laminated Fiberglass, 4' Long Stick, 0.25" Dia, AL/GF, Silver, 50/box                                                                                                                                                                                                   |
| Global Part Name    | BSHTTSW14SB-GF-AL-SR                                                                                                                                                                                                                                                                           |

|                                |       |
|--------------------------------|-------|
| Length L (Imperial)            | 4.0   |
| Length L (Metric)              | 1.22  |
| Bundle Diameter Min (Imperial) | 0.1   |
| Bundle Diameter Min (Metric)   | 2.54  |
| Bundle Diameter Max (Imperial) | 0.20  |
| Bundle Diameter Max (Metric)   | 5.1   |
| Diameter D (Imperial)          | 0.25  |
| Diameter D (Metric)            | 6.35  |
| Nominal Diameter (Imperial)    | 0.25  |
| Nominal Diameter (Metric)      | 6.35  |
| Wall Thickness WT (Imperial)   | 0.042 |
| Wall Thickness WT (Metric)     | 1.06  |

Material Glass fiber with aluminium foil (GF-AL)

Material Shortcut GF-AL

Halogen Free Yes

|                              |                                   |
|------------------------------|-----------------------------------|
| UV Resistant (Yes/No)        | No                                |
| Operating Temperature        | -76°F to +491°F (-60°C to +255°C) |
| Reach Compliant (Article 33) | Yes                               |
| ROHS Compliant               | Yes                               |
| Package Quantity (Imperial)  | 50                                |
| Package Quantity (Metric)    | 50                                |
| Customs Number               | 7019905150                        |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03190](#)