

Specification Sheet

Part Number: CTM20M4



KR/CTM series are designed to provide stability to wire bundles.

These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

Cable Tie Anchor Mount, 0.86 x .61", 0.18" Hole Dia, 0.31" Max Tie Width, PA66, Black, 1000/pkg

Article Number	151-30501
----------------	-----------

Type	CTM2
------	------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.
---------------------	---

Short Description	Cable Tie Anchor Mount, 0.86 x .61", 0.18" Hole Dia, 0.31" Max Tie Width, PA66, Black, 1000/pkg
-------------------	---

Global Part Name	CTM2-PA66-BK
------------------	--------------

Length L (Imperial)	0.86
Length L (Metric)	21.8
Fixation Method	Screw Mount
Width W (Imperial)	0.61
Width W (Metric)	15.5
Cable Ties	T18 - T120
Height H (Imperial)	.37
Height H (Metric)	9.40
Cable Tie Width Max (Imperial)	0.31
Cable Tie Width Max (Metric)	7.9
Mounting Hole Diameter D (Imperial)	0.18
Mounting Hole Diameter D (Metric)	4.6 mm
Mounting Hole Diameter D Max (Metric)	4.6
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CTM20M4](#)