


Specification Sheet

Part Number: 156-02687



Two-piece cable tie and mount allows for a wide range of bundle sizes.
A suitable alternative for metal clamps.

Robust design withstands vibration and displacement forces.

Metal bushing allows for high tightening torque.

2-Piece Cable Tie/Screw Mount, 8" Long, M8 Hole, 2.0" Max Bundle Dia, 50lb, PPS, Silver, 3000/ctn

Article Number 156-02687

Type T50RCPCM8BSET

Color Silver (SR)

Quantity Per bag

Product Description These cable tie mounts attach with a screw or bolt to an existing hole, or secure to a stud with a nut. They provide an attachment point for securing and routing a single bundle. These mounts provide the highest level of fastening for critical cable security.

Short Description 2-Piece Cable Tie/Screw Mount, 8" Long, M8 Hole, 2.0" Max Bundle Dia, 50lb, PPS, Silver, 3000/ctn

Global Part Name T50RCPCM8BSET-PPS-SR

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	7.874
Length L (Metric)	200.0
Fixation Method	Screw Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Height H (Imperial)	0.61

Height H (Metric)	16.0
Mounting Hole Diameter D (Imperial)	0.33
Mounting Hole Diameter D (Metric)	8.4 mm
Material	Polyphenylene Sulfide (PPS)
Material Shortcut	PPS
Material Cable Tie	Polyphenylene Sulfide (PPS)
UV Resistant (Yes/No)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02687](#)