

Specification Sheet

Part Number: 181-00308



Dividers have continuous score lines for smooth breakouts.

Top of the dividers has a double-sided lip which reduces the likelihood of wires falling out during installation.

Wiring Duct Divider, 3" High, PVC, White, 120 ft/carton

|                     |                                                                                                                                                                                                                                                                                              |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 181-00308                                                                                                                                                                                                                                                                                    |
| Type                | DV3                                                                                                                                                                                                                                                                                          |
| Color               | White (WH)                                                                                                                                                                                                                                                                                   |
| Quantity Per        | carton                                                                                                                                                                                                                                                                                       |
| Product Description | Solid-Wall Dividers can be securely mounted into all types of HellermannTyton wiring duct to separate high and low voltage, thus reducing interference. The dividers simply snap or slide into the specially designed mount, instantly creating multiple channels within a single duct size. |
| Short Description   | Wiring Duct Divider, 3" High, PVC, White, 120 ft/carton                                                                                                                                                                                                                                      |
| Global Part Name    | DV3-PVC-WH                                                                                                                                                                                                                                                                                   |

|                        |       |
|------------------------|-------|
| Length L (Imperial)    | 6.0   |
| Length L (Metric)      | 1.83  |
| Width W (Imperial)     | 0.77  |
| Width W (Metric)       | 19.56 |
| Thickness T (Imperial) | 0.07  |
| Thickness T (Metric)   | 1.78  |
| Height H (Imperial)    | 2.85  |
| Height H (Metric)      | 72.40 |

|          |                         |
|----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
|----------|-------------------------|

|                   |     |
|-------------------|-----|
| Material Shortcut | PVC |
|-------------------|-----|

|              |    |
|--------------|----|
| Halogen Free | No |
|--------------|----|

|                       |    |
|-----------------------|----|
| UV Resistant (Yes/No) | No |
|-----------------------|----|

|                       |                |
|-----------------------|----------------|
| Operating Temperature | +122°F (+50°C) |
|-----------------------|----------------|

|                              |    |
|------------------------------|----|
| Reach Compliant (Article 33) | No |
|------------------------------|----|

|                |     |
|----------------|-----|
| ROHS Compliant | Yes |
|----------------|-----|

|                             |                                              |
|-----------------------------|----------------------------------------------|
| Certification/Specification | UL EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A |
| UL Recognized (US)          | Yes                                          |
| Package Quantity (Imperial) | 120.0                                        |
| Package Quantity (Metric)   | 36.58                                        |
| Customs Number              | 3925900000                                   |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[181-00308](#)