

Specification Sheet

Part Number: 169-60004



Durable tubing provides protection of wire harness from friction, vibration, fraying and puncture.

Tubing protects cables and wires against automotive fluids and vibration wear.

Weather resistant material provides protection against water, snow, ice, and the effects of heat or cold.

Nylon material is formulated to withstand high temperatures.

Lateral slit allows fast and easy insertion of wires.

Convoluted Tubing, Slit, 1.25" Dia, PA6, Black with Gray Stripe, 1800ft/carton

Article Number	169-60004
Type	CTN1140
Color	Black with Gray Stripe (BKSTGY)
Quantity Per	carton
Product Description	Convoluted tubing provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. It also can serve to protect valuable wiring circuits. HellermannTyton's convoluted tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat or cold on cables and wires. Available in standard, bulk, and dispenser box packaging. Material is slit.

Short Description	Convuluted Tubing, Slit, 1.25" Dia, PA6, Black with Gray Stripe, 1800ft/carton
Global Part Name	CTN1140-PA6-BK
Technical Description	Convuluted Tubing, Slit, 1-1/4" Dia., PA6, Black w/Gray Stripe
Length L (Imperial)	1800.0
Length L (Metric)	548.6
Variant	Slit
Inner Diameter D (Imperial)	1.257
Inner Diameter D (Metric)	31.93
Diameter D (Imperial)	1.50
Diameter D (Metric)	38.10
Outside Diameter OD (Imperial)	1.50
Outside Diameter OD (Metric)	38.10
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.75
Wall Thickness WT (Imperial)	0.006

Wall Thickness WT (Metric)	0.152
-----------------------------------	-------

Material	Polyamide 6 (PA6)
-----------------	-------------------

Material Shortcut	PA6
--------------------------	-----

Flammability	UL 94 HB
---------------------	----------

Operating Temperature	-40°F to +257°F (-40°C to +125°C)
------------------------------	-----------------------------------

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	1800
------------------------------------	------

Package Quantity (Metric)	548.6
----------------------------------	-------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[169-60004](#)