

Specification Sheet

Part Number: 170-03066



Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.

Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.

Braided Sleeving, Expandable, Flame Retardant, 1.5" Dia, PET, Gray, 40 ft/reel

Article Number	170-03066
Type	BSPFR1128
Color	Gray (GY)
Quantity Per	reel
Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification. This fire extinguishing braided sleeving is ideal for electronic and high tech applications because of its lightweight and durable qualities.
Short Description	Braided Sleeving, Expandable, Flame Retardant, 1.5" Dia, PET, Gray, 40 ft/reel

Global Part Name	BSPFR1128-PET-GY
Length L (Imperial)	40.0
Length L (Metric)	12.2
Bundle Diameter Min (Imperial)	1.0
Bundle Diameter Min (Metric)	25.4
Bundle Diameter Max (Imperial)	2.125
Bundle Diameter Max (Metric)	53.9
Diameter D (Imperial)	1.50
Diameter D (Metric)	38.1
Nominal Diameter (Imperial)	1.5
Nominal Diameter (Metric)	38.1
Material	Polyester (PET)
Material Shortcut	PET
Flammability	FAR 25 Mil-202 FMVSS 302 UL 224 VW-1
Halogen Free	Yes

UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 94 VW-1
UL Recognized (US)	Yes
Package Quantity (Imperial)	40
Package Quantity (Metric)	12.19
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03066](#)