

Specification Sheet

Part Number: 170-03184



Center-slit overlapping design allows quick and easy access to the wires and cables for future maintenance or inspection without disassembly.

Flexible material allows it to easily wrap around a variety of component shapes and sizes, making it easier to use than slit-loom tubing or spiral-wrap materials.

A unique weave pattern provides increased coverage and greater resistance to abrasion, dust and debris.

Overlapping design enhances flexibility, allowing it to shift and bend without exposing wire and cables.

Braided Sleeving, Split Wrap Woven, 3/4" Dia, PET, Black, 150 ft/bulk reel

Article Number	170-03184
Type	BSSWV340B
Color	Black (BK)
Quantity Per	reel
Product Description	Split Wrap Woven Sleeving is a self-closing sleeving manufactured from a unique blend of monofilament and multifilament polyester fibers that resemble a tightly woven material. The wrap around design provides increased flexibility, better coverage and greater resistance from abrasion for wires, cables and assemblies. Can also be used to reduce noise in applications that involve movement, while protecting sensitive electronics and communication systems from dust and debris.

Short Description	Braided Sleeving, Split Wrap Woven, 3/4" Dia, PET, Black, 150 ft/bulk reel
Global Part Name	BSSWV340B-PET-BK
Length L (Imperial)	150.0
Length L (Metric)	45.7
Bundle Diameter Min (Imperial)	0.1
Bundle Diameter Min (Metric)	2.54
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.1
Diameter D (Imperial)	0.75
Diameter D (Metric)	19.1
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.1
Wall Thickness WT (Imperial)	0.027
Wall Thickness WT (Metric)	0.68

Material	Polyester (PET)
Material Shortcut	PET
Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	150.0
Package Quantity (Metric)	45.7
Customs Number	5806322000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[170-03184](#)