

Specification Sheet

Part Number: 181-00254



Narrow fingers reduce fanning of wires to terminal blocks, providing a neater appearance.

Each finger features a double restriction to hold wires in the bottom portion of the duct, simplifying installation.

Mounting holes are uniform in size to those in slotted and solid wall duct but are provided every two inches to accommodate compact designs and provide ease of installation.

Nonpermanent adhesive allows repositioning prior to final installation.

High Density Slotted Wall Wiring Duct, 2" x 5", Adhesive, PVC, Gray, 120ft/Carton

|                     |                                                                                                                                                                                                                                              |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 181-00254                                                                                                                                                                                                                                    |
| Type                | SLHDA2X5                                                                                                                                                                                                                                     |
| Color               | Gray (GY)                                                                                                                                                                                                                                    |
| Quantity Per        | carton                                                                                                                                                                                                                                       |
| Product Description | HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |
| Short Description   | High Density Slotted Wall Wiring Duct, 2" x 5", Adhesive, PVC, Gray, 120ft/Carton                                                                                                                                                            |

|                                         |                         |
|-----------------------------------------|-------------------------|
| <b>Global Part Name</b>                 | SLHDA2X5-PVC-GY         |
| <b>Technical Description</b>            | Adhesive                |
| <b>Length L (Imperial)</b>              | 6.0                     |
| <b>Length L (Metric)</b>                | 1.83                    |
| <b>Fixation Method</b>                  | Adhesive                |
| <b>Width W (Imperial)</b>               | 2.0                     |
| <b>Width W (Metric)</b>                 | 50.8                    |
| <b>Height H (Imperial)</b>              | 5.07                    |
| <b>Height H (Metric)</b>                | 128.8                   |
| <b>Mounting Hole Centers (Imperial)</b> | 2.0                     |
| <b>Material</b>                         | Polyvinylchloride (PVC) |
| <b>Material Shortcut</b>                | PVC                     |
| <b>Flammability</b>                     | Self-extinguishing      |
| <b>Halogen Free</b>                     | No                      |

|                                     |                                                  |
|-------------------------------------|--------------------------------------------------|
| <b>Operating Temperature</b>        | +122°F (+50°C)                                   |
| <b>Reach Compliant (Article 33)</b> | No                                               |
| <b>ROHS Compliant</b>               | Yes                                              |
| <b>Certification/Specification</b>  | EN 50085-2-3_1A EN 50085-1:2005 + A1:2013 CSA UL |
| <b>UL Recognized (US)</b>           | Yes                                              |
| <b>Package Quantity (Imperial)</b>  | 120                                              |
| <b>Package Quantity (Metric)</b>    | 36.58                                            |
| <b>Customs Number</b>               | 3925900000                                       |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[181-00254](#)