

Specification Sheet

Part Number: 184-22032



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance. Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High-Density Slotted-Wall Wiring Duct, 3" x 4", Non-Adhesive, PVC, Black, 30ft/box

Article Number	184-22032
Type	SLHD3X4
Color	Black (BK)
Quantity Per	box
Product Description	HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High-Density Slotted-Wall Wiring Duct, 3" x 4", Non-Adhesive, PVC, Black, 30ft/box

Global Part Name	SLHD3X4-PVC-BK
------------------	----------------

Length L (Imperial)	6.0
---------------------	-----

Length L (Metric)	1.83
-------------------	------

Width W (Imperial)	3.0
--------------------	-----

Width W (Metric)	76.2
------------------	------

Height H (Imperial)	4.07
---------------------	------

Height H (Metric)	103.4
-------------------	-------

Mounting Hole Centers (Imperial)	2.0
----------------------------------	-----

Material	Polyvinylchloride (PVC)
----------	-------------------------

Material Shortcut	PVC
-------------------	-----

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Operating Temperature	+122°F (+50°C)
-----------------------	----------------

Reach Compliant (Article 33)	No
------------------------------	----

ROHS Compliant	Yes
----------------	-----

Certification/Specification	CSA EN 50085-1:2005 + A1:2013 EN 50085-2-3_1A UL
UL Recognized (US)	Yes
Package Quantity (Imperial)	30.0
Package Quantity (Metric)	9.14
Customs Number	3925900000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[184-22032](#)