

Specification Sheet

Part Number: TSRPI-JBD2



Junction boxes can be used for electrical or data outlets.

Rubber-based foam tape adhesive with high ultimate bond strength, which conforms to any surface.

Dual Gang Junction Box, 2.77" Deep, 3-Piece, PVC, Ivory, 1/bg

Article Number	250-00205
----------------	-----------

Type	TSRP-JBD2
------	-----------

Color	Ivory (IV)
-------	------------

Quantity Per	EA
--------------	----

Product Description	Offered in a dual or single gang format, HellermannTyton's power-rated junction boxes are versatile enough for any network cabling application. Available in varying depths, these boxes are all equipped with concentric knockouts on all four sides for every TSRP size of raceway to eliminate routing and installation inconvenience. All junction boxes come with adhesive strips on the back of the base and #6 screws to secure the box to the base.
---------------------	---

Short Description	Dual Gang Junction Box, 2.77" Deep, 3-Piece, PVC, Ivory, 1/bg
-------------------	---

Global Part Name	TSRP-JBD2-PVC-BGE
------------------	-------------------

Length L (Imperial)	4.94
---------------------	------

Length L (Metric)	125.48
-------------------	--------

Width W (Imperial)	5.02
--------------------	------

Width W (Metric)	127.51
------------------	--------

Height H (Imperial)	2.77
---------------------	------

Height H (Metric)	70.36
-------------------	-------

Material	Polyvinylchloride (PVC)
----------	-------------------------

Material Shortcut	PVC
-------------------	-----

Flammability	UL 94 V-0
--------------	-----------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Operating Temperature	+122°F (+50°C)
-----------------------	----------------

Reach Compliant (Article 33)	No
------------------------------	----

ROHS Compliant	Yes
----------------	-----

UL Listed (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3925900000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TSRPI-JBD2](#)