

Specification Sheet

Part Number: 333-41511

Thin wall, flexible 3 to 1 shrink ratio material accommodates a wide range of component shapes and diameters.

Meets UL224 VW-1 specifications, making it ideal for high heat applications (excludes clear tubing).

Polyolefin material provides excellent insulation and mechanical strength with good resistance to solvents, oils and fuels.

Available in bulk reels, sticks and convenience bags (HIS-3 bags), for small to large volume applications.



Heat Shrink Tubing, 4' Long Stick, 3:1 Shrink Ratio, 3/8", 9.5/3.0 Dia, PO, Black, 15/pkg

Article Number	333-41511
----------------	-----------

Type	TFN31-ST-9/3
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	lengths
--------------	---------

Product Description	TFN31 series heat shrink tubing features a flexible, thin wall and highly flame retardant polyolefin material with a higher operating temperature range than general-use heat shrink tubing. and offers good resistance to solvents, oils and fuels. The 3 to 1 shrink ratio accommodates a variety of component shapes and sizes. TFN31 tubing is available in bulk reels, sticks and convenience bags (HIS-3 bags), for projects of all sizes.
---------------------	--

Short Description	Heat Shrink Tubing, 4' Long Stick, 3:1 Shrink Ratio, 3/8", 9.5/3.0 Dia, PO, Black, 15/pkg
Global Part Name	TFN31-ST-9/3-PO-X-BK
Length L (Metric)	1.22
Variant	Thin-Wall
Nominal Diameter (Imperial)	0.38
Nominal Diameter (Metric)	9
Wall Thickness WT (Imperial)	.029
Wall Thickness WT (Metric)	0.75
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-58°F to +275°F (-50°C to +135°C)

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 224 CSA C22.2 no. 198.1-06
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	15
Package Quantity (Metric)	15
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[333-41511](#)