

Specification Sheet

Part Number: 596-00905

- Made with UV-stable inks and materials for durability and weather resistance.
- Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.
- High abrasion and scuff resistance for high-performance labeling.
- Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.



Arc Flash Label, WARNING ARC FLASH AND SHOCK HAZARD, 5.0" x 3.75", PET, Orange/White, 10/pkg

Article Number	596-00905
Type	AF5X35W
Color	Orange (OG)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC 2014, 2017 and 2020 code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC 2014, 2017 and 2020 code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Arc Flash Label, WARNING ARC FLASH AND SHOCK HAZARD, 5.0" x 3.75", PET, Orange/White, 10/pkg
Global Part Name	AF5X35W-840/281-OG
Technical Description	Arc Flash Label, Warning- Arc Flash and Shock Hazard, 5.0" X 3.75",Orange/White
Width W (Imperial)	5.00
Width W (Metric)	127
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	3.75
Height H (Metric)	95.25

Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Halogen Free	Yes
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 NEC2014 NEC2020 NEC2011
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Labels per Column	1
Labels per Row	1

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00905](#)