

Specification Sheet

Part Number: 596-00255

Made with UV-stable inks and materials for durability and weather resistance.
Reflective properties to meet applicable NEC code requirements for reflective identification.
Supplied with an aggressive adhesive to ensure long life.



Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, Reflective, MAIN PV AC DISCONNECT, 5.5" x 1.75", VL, Red, 50/roll

Article Number	596-00255
Type	MPVACDIS
Color	Red (RD)
Quantity Per	roll
Product Description	HellermannTyton Pre-Printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code (NEC) and the International Fire Code (IFC) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, Reflective, MAIN PV AC DISCONNECT, 5.5" x 1.75", VL, Red, 50/roll
Global Part Name	MPVACDIS-505/281-RD
Technical Description	Pre-Printed Solar Label, Reflective, "MAIN PV AC DISCONNECT", 5.5" X 1.75", Red
Local Order Number 2	Cross Reference = 10 per pack: 596-00676; Metal Solar Placard 5 pack: 596-00861
Length L (Imperial)	5.5
Length L (Metric)	139.7
Width W (Imperial)	5.5
Width W (Metric)	139.7
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.75
Height H (Metric)	44.40
Material	Type 505/281, UV-stabilized reflective vinyl with clear polyester laminate (505/281)

Material Shortcut	505/281
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017 IFC 2012 UL 969 NEC2011
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00255](#)