

Specification Sheet

Part Number: 596-00382



Thermal transfer labels are made with high-performance materials for long-term industrial applications. Labels can be printed in any standard thermal transfer printer giving the user options for printing and eliminating the need to be dedicated to one printer model. The labels are available in a wide variety of sizes so that finding a label for a particular application is easy.

Phase label, 1" x .5", PET, White, 2500/roll

|                     |                                                                                                                                           |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 596-00382                                                                                                                                 |
| Type                | PLW3P                                                                                                                                     |
| Color               | White (WH)                                                                                                                                |
| Quantity Per        | roll                                                                                                                                      |
| Product Description | Phase labels are microperforated between each label so that it can be applied as one strip to the panel or broken into individual labels. |
| Short Description   | Phase label, 1" x .5", PET, White, 2500/roll                                                                                              |
| Global Part Name    | PLW3P-PET-WH                                                                                                                              |

|                                  |                                   |
|----------------------------------|-----------------------------------|
| <b>Technical Description</b>     | Phase label, 1" X .5", PET, White |
| <b>Local Order Number 2</b>      | 596-00382                         |
| <b>Width W (Imperial)</b>        | 1.0                               |
| <b>Width W (Metric)</b>          | 25.4                              |
| <b>Thickness T (Metric)</b>      | 64.0                              |
| <b>Height H (Imperial)</b>       | 0.5                               |
| <b>Height H (Metric)</b>         | 12.7                              |
| <b>Width of Liner (Metric)</b>   | 85.09                             |
| <b>Width of Liner (Imperial)</b> | 3.35                              |
| <b>Material</b>                  | Polyester (PET)                   |
| <b>Material Shortcut</b>         | PET                               |
| <b>Adhesive</b>                  | Acrylic                           |
| <b>Halogen Free</b>              | No                                |
| <b>Operating Temperature</b>     | -40°F to +300°F (-40°C to +149°C) |

|                                     |     |
|-------------------------------------|-----|
| <b>Reach Compliant (Article 33)</b> | Yes |
|-------------------------------------|-----|

|                       |     |
|-----------------------|-----|
| <b>ROHS Compliant</b> | Yes |
|-----------------------|-----|

|                           |     |
|---------------------------|-----|
| <b>UL Recognized (US)</b> | Yes |
|---------------------------|-----|

|                                    |      |
|------------------------------------|------|
| <b>Package Quantity (Imperial)</b> | 2500 |
|------------------------------------|------|

|                                  |      |
|----------------------------------|------|
| <b>Package Quantity (Metric)</b> | 2500 |
|----------------------------------|------|

|                       |            |
|-----------------------|------------|
| <b>Customs Number</b> | 3919102055 |
|-----------------------|------------|

|                          |   |
|--------------------------|---|
| <b>Labels per Column</b> | 3 |
|--------------------------|---|

|                       |   |
|-----------------------|---|
| <b>Labels per Row</b> | 3 |
|-----------------------|---|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00382](#)