

Specification Sheet

Part Number: 596-00816

Made with UV-stable inks and materials for durability and weather resistance.
Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.
High abrasion and scuff resistance for high-performance labeling.
Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

VOLTAJE NOMINAL DE OPERACIÓN DE CA	
FRECUENCIA NOMINAL DE OPERACIÓN DE CA	
POTENCIA MÁXIMA DE CA	
CORRIENTE MÁXIMA DE CA	
SOBRECORRIENTE NOMINAL MÁXIMA DEL DISPOSITIVO	
PARA PROTECCIÓN DEL MODULO DE CA	

Solar Label, Printable, Spanish, AC Module, 4.0" x 2.0", PET, Red, 50/roll

Article Number	596-00816
Type	AC2011S
Color	Red (RD)
Quantity Per	roll
Product Description	Designed with cross-laminated UV stable materials, these variable print solar installation labels are designed to accept printing from any standard thermal transfer printer using a resin-based ink ribbon for the best durability. Print your voltage information directly on the label and then laminate with an optional clear acrylic laminate material for added protection. These labels can be used to print disconnecting means and breaker series directly on the labels for a more professional result and a smoother inspection process.

Short Description	Solar Label, Printable, Spanish, AC Module, 4.0" x 2.0", PET, Red, 50/roll
Global Part Name	AC2011S-840/281-RD
Technical Description	Printable Solar Label, Spanish Version, AC MODULE LABEL, 4.0" X 2.0", Red
Local Order Number 2	English Version: 596-00252
Width W (Imperial)	4.0
Width W (Metric)	101.6
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.0
Height H (Metric)	50.8
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic

Halogen Free	Yes
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CSA 66956
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00816](#)