


Specification Sheet

Part Number: 596-00923

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.  
Aggressive adhesive ensures strong bond, even on powder coated surfaces.  
Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.



Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Metal Solar Placard, Engravable, PV AC DISCONNECT, 3.75" x 1.0", AA, Black, 5/pkg

Article Number	596-00923
Type	PVACDIS17M5ENG
Color	Black (BK)
Quantity Per	pack
Product Description	Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, engravable placards are designed to meet industry codes. Engravable placards have a black area that can be engraved using standard engraving equipment.

<b>Short Description</b>	Metal Solar Placard, Engravable, PV AC DISCONNECT, 3.75" x 1.0", AA, Black, 5/pkg
<b>Global Part Name</b>	PVACDIS17M5ENG-AA-BK
<b>Technical Description</b>	3.75" X 1" Black text on aluminum background that reads as: "PHOTOVOLTAIC AC DISCONNECT. RATED AC OUTPUT CURRENT. NOMINAL OPERATING AC VOLTAGE." 5 per pack. Nameplate can be used with standard engraving equipment to add variable data.
<b>Length L (Imperial)</b>	1.0
<b>Length L (Metric)</b>	25.4
<b>Width W (Imperial)</b>	3.75
<b>Width W (Metric)</b>	95.25
<b>Thickness T (Metric)</b>	64.0
<b>Height H (Imperial)</b>	1.0
<b>Height H (Metric)</b>	25.40
<b>Material</b>	Anodized Aluminum (AA)
<b>Material Shortcut</b>	AA
<b>Adhesive</b>	Ultra High Bond Permanent Acrylic Adhesive

<b>Halogen Free</b>	No
<b>Adhesive Operating Temperature</b>	from +50°F (from +10°C)
<b>Operating Temperature</b>	-40°F to +203°F (-40°C to +95°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	NEC2017
<b>Warranty (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	5
<b>Package Quantity (Metric)</b>	5
<b>Customs Number</b>	3919102055
<b>Labels per Column</b>	1
<b>Labels per Row</b>	1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00923](#)