

Specification Sheet

Part Number: FSTTBAXXFA11



Compact size makes it ideal for restoration use, distribution drops, Distributed Antenna Systems (DAS) and Remote Radio Head (RRH/RRU) applications.

Aerial mounting, underground vault or direct burial for installation where fibers are needed.

Mid span possible for simple routing within Passive Optical Networks (PON).

FST, 4 Port, 1 Hellapon Small Tray (12 fiber), PP, Black, 1/pkg

Article Number	857-00850
Type	FSTTB-AXXFA11
Color	Black (BK)
Quantity Per	kit

Product Description	<p>The FST is a compact, cap-ended, ready-access, fiber-optic splice closure for use in aerial, underground and directly buried installations. Its small size, port flexibility and value make the FST popular for splicing low fiber count distribution cables in FTTH, FTTC, trunk and campus networks, as well as CATV and CCTV installations. The 4-port base configuration offers three round ports and one oval port for loop-through applications. Cover is environmentally sealed to the base using a rolling O-ring. Cable entry/exit points in the base are environmentally sealed using either Cablelok mechanical seals or heat-shrink sleeves.</p>
Short Description	FST, 4 Port, 1 Hellapon Small Tray (12 fiber), PP, Black, 1/pkg
Global Part Name	FSTTB-AXXFA11
Technical Description	<p>The FST 4 Port closure is supplied with a Polypropylene base. The base configuration of 3 round ports and 1 oval port covers a cable diameter range of 4.0 – 16.5mm when using Cablelok mechanical seals and 6.0 – 22.0mm when using heatshrink. The mounting system is manufactured from Grade 304 stainless steel and is supplied with 1 x Hellapon Small Tray with 3A Splice Bridges giving a maximum of 12 fibre splices. The tubed closure and the position of the mounting system allows for ease of access and traceability of the fibre on to the trays. The trays are white which makes it easy to see the colour of the fibre elements as they are routed through the fibre management system and on to the trays.</p>
Contents of pkg/kit	<p>FST 4 Port Base A-Length Cover (Dome) Quick Release Clamp Sealing O-Ring Tray Support Frame Anchor Fixing Kit Transportation Tubing Isopropyl Alcohol Wipes Desiccant Installation Guide Marker Kit:Red Marker 1 - 12; Green Marker 1 - 12</p>
Port Count	3 1
Variant	Outdoor Enclosure

Material	Polypropylene (PP)
-----------------	--------------------

Material Shortcut	PP
--------------------------	----

Package Quantity (Imperial)	1
------------------------------------	---

Package Quantity (Metric)	1
----------------------------------	---

Customs Number	9030400000
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FSTTBAXXFA11](#)