

Specification Sheet

Part Number: TYHC27



Handi-Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing. Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card. Markers are pre-printed so no additional post printing is required, saving time and money. Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.

Handi-Card Wire and Cable Markers, .25" x 1.5", Solid #27, 36 Per Card, TYHC, White, 25/pkg

Article Number	598-00050
Type	TYHC27
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.

<b>Short Description</b>	Handi-Card Wire and Cable Markers, .25" x 1.5", Solid #27, 36 Per Card, TYHC, White, 25/pkg
<b>Global Part Name</b>	TYHC27-TYHC-WH
<b>Length L (Imperial)</b>	1.5
<b>Length L (Metric)</b>	38.1
<b>Width W (Imperial)</b>	0.25
<b>Width W (Metric)</b>	6.35
<b>Bundle Diameter Min (Imperial)</b>	.13
<b>Bundle Diameter Min (Metric)</b>	3.40
<b>Bundle Diameter Max (Imperial)</b>	.29
<b>Bundle Diameter Max (Metric)</b>	7.50
<b>Height H (Imperial)</b>	1.50
<b>Height H (Metric)</b>	38.10
<b>Outside Diameter Max (Imperial)</b>	.290
<b>Outside Diameter Min (Metric)</b>	3.40
<b>Outside Diameter Min (Imperial)</b>	.130

<b>Outside Diameter Max (Metric)</b>	7.50
<b>Material</b>	Vinyl Cloth (TYHC)
<b>Material Shortcut</b>	TYHC
<b>Adhesive</b>	Rubber
<b>Adhesive Operating Temperature</b>	-40°F to +248°F (-40°C to +120°C)
<b>Operating Temperature</b>	-40°F to +248°F (-40°C to +120°C)
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	25
<b>Package Quantity (Metric)</b>	25
<b>Customs Number</b>	5903103000
<b>Labels per Column</b>	1
<b>Labels per Row</b>	36



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TYHC27](#)