

Specification Sheet

Part Number: CCP-SAP-W



Fully water sealed, achieving an IP-68 (NEMA 6P) rating, for use in wall or handhole installations.

Separate inbound/outbound access points ensure cable sealing and segregation.

Single subscriber splice or patch to connect a home or outdoor device.

Customer Connection Point, with SC-APC Simplex Adapter and 1 m SC-APC Pigtail, PC, White, 1/pkg

Article Number	904-01127
-----------------------	-----------

Type	CCP-SAP-W
-------------	-----------

Color	White (WH)
--------------	------------

Quantity Per	EA
---------------------	----

Product Description	<p>The Customer Connection Point (CCP) is manufactured from UL 94 V-0 and UV stable black polycarbonate and has a fully detachable snap-on lid. The closure has 2 separate cable access points which are sealed with a silicon cable entry kit (cable diameter range 4.6 mm - 5.6 mm) to maintain the IP68 rating. A GORE-TEX breather membrane is fitted to the lid to prevent condensation forming in the base of the closure. The unit can be supplied with one SC Simplex or LC Duplex and matching pigtails and provides splice management for two heat shrink splices. Internal fiber management features ensure that a 30 mm minimum bend radius is maintained within the closure and provides fiber storage capacity for any excess fiber.</p>
----------------------------	--

Short Description	Customer Connection Point, with SC-APC Simplex Adapter and 1 m SC-APC Pigtail, PC, White, 1/pkg
Global Part Name	CCP-SAP-W-PC-WH
Contents of pkg/kit	CCP Enclosure (White), 2x Cable Entry Lock Nut, 2x Cable Entry Seal and Seal Plug (4.6–5.6 mm), CableLok Lubricating Cloth, Fiber Routing Adhesive Disk, 2x Strength Member Fixing Screws, 1x SC/APC Adapter 1x SC/APC 900um 1m Pigtail, Installation Instructions
Port Count	2
Variant	Outdoor Enclosure
Width W (Imperial)	3.5
Width W (Metric)	89.0
Height H (Imperial)	6.30
Height H (Metric)	160.0
Depth D (Imperial)	1.10
Depth D (Metric)	28.0
Material	Polycarbonate (PC)
Material Shortcut	PC

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536908085
Weight (Metric)	0.142
Weight (Imperial)	0.313

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CCP-SAP-W](#)