

Specification Sheet

Part Number: ET660



PVC Tape is ideal for general purpose electrical applications. Economical way to splice, terminate and insulate wire and cables. Meets Mil-Std. MIL-1-7798-A.

|                     |                                                                                                                                                                                                                                                                                                                                                                                                        |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 904-00008                                                                                                                                                                                                                                                                                                                                                                                              |
| Type                | ET66                                                                                                                                                                                                                                                                                                                                                                                                   |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                                                                             |
| Quantity Per        | reel                                                                                                                                                                                                                                                                                                                                                                                                   |
| Product Description | PVC electrical tape provides fast and easy color coding, cable splicing, terminating, and wire insulating. These comformable high quality tapes have exceptional surface and adhesive characteristics. Tape is applied by overlapping each layer 50% and using tension. After the tape is adhered, the memory of the tape returns, tightening the seal and making the taped area even more waterproof. |
| Short Description   | Electrical Tape, .75" x 66' Roll, 7.0 mil Thick, PVC, Black, 10 rolls/pkg                                                                                                                                                                                                                                                                                                                              |
| Global Part Name    | ET66-PVC-BK                                                                                                                                                                                                                                                                                                                                                                                            |

|                                            |                                   |
|--------------------------------------------|-----------------------------------|
| <b>Minimum Tensile Strength (Imperial)</b> | 15.4                              |
| <b>Length L (Imperial)</b>                 | 66.0                              |
| <b>Length L (Metric)</b>                   | 20.12                             |
| <b>Width W (Imperial)</b>                  | 0.75                              |
| <b>Width W (Metric)</b>                    | 19.05                             |
| <b>Thickness T (Imperial)</b>              | 7.0                               |
| <b>Material</b>                            | Flexible Polyvinyl Chloride (PVC) |
| <b>Material Shortcut</b>                   | PVC                               |
| <b>US MIL SPEC</b>                         | MIL-1-7798-A                      |
| <b>Operating Temperature</b>               | +20°F to 176°F (-7°C to +80°C)    |
| <b>Package Quantity (Imperial)</b>         | 10                                |
| <b>Package Quantity (Metric)</b>           | 10                                |
| <b>Customs Number</b>                      | 3919102020                        |

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[ET660](#)