

**date** 06/24/2019

page 1 of 5

# MODEL: CMC-5044TF-A | DESCRIPTION: ELECTRET CONDENSER MICROPHONE

#### **FEATURES**

- omnidirectional
- analog
- solder pads





#### **ELECTRICAL**

parameter	conditions/description	min	typ	max	units
directivity	omnidirectional				
sensitivity (S)	at 1 kHz (0 dB = 1 V/Pa)	-47	-44	-41	dB
supply voltage (VDD)			2.0	10	V
current consumption	$V_{DD} = 2.0 \text{ V, RL} = 2.2 \text{ k}\Omega$			0.5	mA
sensitivity reduction	V <sub>DD</sub> = 2.0 ~ 1.5 V			-3	dB
frequency (f)		100		20,000	Hz
signal to noise ratio (S/N)	at 1 kHz, Pin = 1 Pa (A-weighted)		60		dBA
total harmonic distortion (THD)	at 115 dB SPL, 1 kHz			10	%
acoustic overload point (AOP)	at 1 kHz			115	dB SPL
output impedance (Zout)	at 1 kHz			2.2	kΩ

Notes: 1. All specifications measured at 5~35°C, humidity at 45~85%, under 86~106 kPa pressure, unless otherwise noted.

## **ENVIRONMENTAL**

parameter	conditions/description	min	typ	max	units
operating temperature		-20		70	°C
storage temperature		-20		70	°C
hand soldering	for 2±0.5 seconds	310	320	330	°C
RoHS	yes				

## **MECHANICAL**


parameter	conditions/description	min	typ	max	units
dimensions	Ø6.0 x 5				mm
acoustic port	top				
material	AL				
terminals	solder pads				
weight			0.30		g


## **MECHANICAL DRAWING**


units: mm

tolerance: ±0.2 mm


TERMINAL CONNECTIONS			
TERM.	FUNCTION		
1	Output (+)		
2	GND (-)		








## **APPLICATION CIRCUIT**



### **PACKAGING**

Small Box Size: 63 x 63 x 8 mm Medium Box Size: 125 x 65 x 45 mm Carton Size: 230 x 230 x 270 mm Small Box QTY: 100 pcs per box Carton QTY: 40,000 pcs per carton



#### **REVISION HISTORY**

rev.	description	date
1.0	initial release	07/21/2008
1.01	changed color of mesh cloth	06/24/2019

The revision history provided is for informational purposes only and is believed to be accurate.



**Headquarters** 20050 SW 112th Ave. Tualatin, OR 97062 **800.275.4899** 

Fax 503.612.2383 cui.com techsupport@cui.com

CUI offers a one (1) year limited warranty. Complete warranty information is listed on our website.

CUI reserves the right to make changes to the product at any time without notice. Information provided by CUI is believed to be accurate and reliable. However, no responsibility is assumed by CUI for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CUI Inc.: