


UNCONTROLLED DOCUMENT
WILL NOT BE UPDATED



68-026-01	.514	.090	1.250	.031 ∇ .100	GREEN
68-024S-01	.514	.070	1.250	.027 ∇ .050	GOLD
68-024-01	.514	.070	1.250	.027 ∇ .100	GOLD
68-023-01	.514	.090	1.250	.029 ∇ .100	BLACK
68-022-01	.514	.093	1.250	.034 ∇ .100	BROWN
68-020S-01	.514	.094	1.250	.042 ∇ .020	RED
68-020-01	.514	.094	1.250	.042 ∇ .100	RED
68-016-01	.514	.125	1.250	.065 ∇ .100	BLUE
68-012-01	.514	.156	1.250	.097 ∇ .100	YELLOW
68-008-01	.542	.209	1.250	.150 ∇ .100	RED
PART NO.	"A"	ϕ "B"	"C"	"D"	COLOR

RESTRICTED & CONFIDENTIAL		ITEM		PART NO.	QTY.	DESCRIPTION/REMARKS	
CONFIDENTIAL PROPERTY OF DANIELS MANUFACTURING CORP. NOT TO BE DISCLOSED TO OTHERS, REPRODUCED OR USED FOR ANY OTHER PURPOSE, EXCEPT AS AUTHORIZED IN WRITING BY DANIELS MANUFACTURING. MUST BE RETURNED TO DANIELS MANUFACTURING CORP. ON COMPLETION OF ORDER OR OTHER PURPOSE FOR WHICH LENT.		DRN.	JMC	DATE 2-11-00		 DANIELS MANUFACTURING CORP. ORLANDO, FLORIDA CAGE 11851	
		CHK'D.	JWJ	DATE 2-11-00			
		APP'D.		DATE			
		APP'D.		DATE			
DO NOT SCALE DRAWING		NOTE: THIS DRAWING IS AN OUTLINE DRAWING OF THE RESPECTIVE DMC PART NUMBER INDICATED. ACTUAL DMC PART NUMBER IS DRAWING NUMBER WITHOUT THE "-ENV" SUFFIX.		TITLE		TIP, PIN TESTER ENVELOPE DRAWING	
				WHERE USED:			
				SIZE B	SCALE NTS	CAD P/N 68-XXX-01-ENV	SHEET OF 1 1
				POSTING		DWG. NO. 68-XXX-01-ENV	REV. 5

REVISIONS				
REV. SYM.	E.C.O. NUMBER	DESCRIPTION		BY DATE
5		ADDED 68-020S-01		K. KOONS 6.16.08
				D. EBY 8.16.08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Daniels Manufacturing:](#)

[68-012-01](#)