

Users must ensure they are using the correct revision.


REVISIONS				
REV. SYM.	E.C.O. NUMBER	DESCRIPTION	BY DATE	APP'D DATE
A	23072	ORIGINAL RELEASE	ENF 9-17-13	RRR 9-17-13

MIL SPEC EMI TERMINATION BANDS				
DMC PART NUMBER	AS85049/128 SPEC NUMBER	DESCRIPTION	LENGTH (REF)	WIDTH (REF)
DBS-128-1	M85049/128-1	1/4" FLAT BAND WELDED BUCKLE	14.00	.245
DBS-128-2	M85049/128-2	1/4" COILED BAND WELDED BUCKLE	14.00	.245
DBS-128-3	M85049/128-3	1/4" FLAT BAND STAMPED BUCKLE	14.25	.245
DBS-128-4	M85049/128-4	1/4" COILED BAND STAMPED BUCKLE	14.25	.245
DBS-128-5	M85049/128-5	1/8" FLAT BAND WELDED BUCKLE	9.50	.118
DBS-128-6	M85049/128-6	1/8" COILED BAND WELDED BUCKLE	9.50	.118
DBS-128-7	M85049/128-7	1/8" FLAT BAND STAMPED BUCKLE	8.13	.115
DBS-128-8	M85049-128-8	1/8" COILED BAND STAMPED BUCKLE	8.13	.115

REQUIREMENTS:

1. MADE IN AMERICA
2. CONFORMS TO DFARS 252.225-7014, Preference for Domestic Specialty metals clause and FAR 52.225-5 Trade Agreement Act
3. MUST BE QPL LISTED TO AS85049/128 STANDARD

NOTES:

RESTRICTED & CONFIDENTIAL CONFIDENTIAL PROPERTY OF DANIELS MANUFACTURING CORP. NOT TO BE DISCLOSED TO OTHERS, REPRODUCED OR USED FOR ANY OTHER PURPOSE, EXCEPT AS AUTHORIZED IN WRITING BY DANIELS MANUFACTURING. MUST BE RETURNED TO DANIELS MANUFACTURING CORP. ON COMPLETION OF ORDER OR OTHER PURPOSE FOR WHICH LENT.	MATERIAL HEAT TREAT FINISH	ITEM	PART NO.	QTY.	DESCRIPTION/REMARKS			
		DRN.	ENF	DATE 9-17-13	 DANIELS MANUFACTURING CORP. ORLANDO, FLORIDA CAGE 11851			
		CHK'D.	RRR	DATE 9-17-13				
		APP'D.		DATE	TITLE EMI TERMINATION BAND, MIL-SPEC			
DO NOT SCALE DRAWING		APP'D.		DATE	WHERE USED:			
		APP'D.		DATE				
		TOLERANCE: UNLESS OTHERWISE SPECIFIED FRACTIONS±1/32 ANGLES±1/2° DECIMALS: .X: ±.020 .XX: ±.010 .XXX: ±.005 .XXXX: ±.0005 REMOVE BURRS & BREAK SHARP EDGES .005-.015			SIZE A	SCALE NTS	CAD P/N DBS-128-X	SHEET OF 1 1
					POSTING	P/N DBS-128-X	REV. A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Daniels Manufacturing:](#)

[DBS-128-3](#) [DBS-128-4](#) [DBS-128-5](#) [DBS-128-6](#) [DBS-128-7](#) [DBS-128-2](#) [DBS-128-1](#) [DBS-128-8](#) [DBS-128-9](#)