

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

1. REPLACEMENT PROBE TIP, 5 mm, THREADED, FOR GENERAL PURPOSE AND GE SERIES OSCILLOSCOPE PROBES.
2. SPECIFICATIONS:
INSULATOR: POLYAMIDE (NYLON)
CONTACT: BRASS, GOLD PLATED
3. RATING:
VOLTAGE: 300 V CAT II
CURRENT: 1 A MAX.
TEMPERATURE: 0° C TO +50°C

CE DECLARATION OF CONFORMITY
CONFORMS TO RoHS 2, ANNEX III 6(c) EXEMPTION.
4. STANDARD PACKAGING:
INDIVIDUAL TIPS: 10 PCS. PER PACK.


PART NUMBER

CT2711A-#


COLOR: 0 - BLACK
8 - GREY

REVISIONS

| REV. | DESCRIPTIONS | DATE | APPROVED |
|------|-----------------------|---------|----------|
| — | CLASS A RELEASED | 7/11/99 | |
| A | UPDATED CONFIGURATION | 1/1/16 | |



THIRD ANGLE PROJECTION



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
FRACTIONS DECIMALS
± 1/32 .XX ± .02
.XXX ± .005
DO NOT SCALE DRAWING

MATERIAL

FINISH

NEXT ASSY

USED ON

APPLICATION

CONTRACT NO.

APPROVALS

DATE

DRAWN WDH

7/11/99

CHECKED

ENGR.

DESIGN ACTIVITY

Cal Test Electronics

22820 Savi Ranch Parkway
Yorba Linda, CA 92887-4610

TITLE

**REPLACEMENT TIP, 5 mm, THREADED,
OSCILLOSCOPE PROBE**

SIZE

A

CAGE CODE

43F45

DWG. NO.

P2711A0

REV.

A

SCALE 1:1

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2711A-8](#) [CT2711A-0](#)